

ebm-papst Mulfingen GmbH & Co. KG

Bachmühle 2 · D-74673 Mulfingen

Phone +49 7938 81-0

Fax +49 7938 81-110

info1@de.ebmpapst.com

www.ebmpapst.com

Limited partnership · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRA 590344

General partner Elektrobau Mulfingen GmbH · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRB 590142

Nominal data


Type	A1G200-AH77-52	
Motor	M1G074-BF	
Nominal voltage	VDC	24
Method of obtaining data		fa
Speed (rpm)	min ⁻¹	2950
Power consumption	W	55
Current draw	A	2.6
Max. back pressure	Pa	120
Max. back pressure	inH ₂ O	0.48
Min. ambient temperature	°C	-25
Max. ambient temperature	°C	60

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment
Subject to change

Technical description

Weight	1.4 kg
Fan size	200 mm
Rotor surface	Painted black
Impeller material	Sheet steel, painted black
Number of blades	9
Airflow direction	"V"
Direction of rotation	Counterclockwise, viewed toward rotor
Degree of protection	IP42
Insulation class	"B"
Moisture (F) / Environmental (H) protection class	F0
Max. permitted ambient temp. for motor (transport/storage)	+80 °C
Min. permitted ambient temp. for motor (transport/storage)	-40 °C
Installation position	Any
Condensation drainage holes	None
Mode	S1
Motor bearing	Ball bearing
Technical features	- Tach output - Motor current limitation - Soft start - Control input 0-10 VDC / PWM
EMC immunity to interference	According to EN 61000-6-2 (industrial environment)
EMC interference emission	According to EN 55022 (Class B, household environment)
Motor protection	Reverse polarity and locked-rotor protection
With cable	Variable
Conformity with standards	EN 60950-1
Approval	UL 1004-1; EAC; CSA C22.2 No. 77


Product drawing



1	Direction of air flow "V"
2	Max. clearance for screw 6 mm
3	Cable PVC AWG20, 4x crimped splices


Connection diagram

Customer circuit




Connection

Fan / Motor



No.	Conn.	Designation	Color	Function/assignment
1	1	Un +24 VDC	red	Power supply 24 VDC, maximum ripple 3.5 %
1	2	0-10 VDC	yellow	Control input Re > 100k
1	3	Tach	white	Tach output, 3 pulses per revolution, Isink max = 10 mA
1	4	GND	blue	Reference ground

Curves: Air performance



Measurement: LU-48037-1
 Measurement: LU-48036-1
 Measurement: LU-48038-1

Air performance measured according to ISO 5801 installation category A. For detailed information on the measurement setup, contact ebm-papst. Intake sound level: Sound power level according to ISO 13347 / sound pressure level measured at 1 m distance from fan axis. The values given are valid under the specified measuring conditions and may vary due to conditions of installation. For deviations from the standard configuration, the parameters have to be checked on the installed unit.

Measured values

	U	n	P _{ed}	I	qv	p _{fs}	qv	p _{fs}
	V	min ⁻¹	W	A	m³/h	Pa	CFM	inH2O
1	28	3285	73	2.91	1205	0	710	0.00
2	28	3190	76	3.01	1115	38	655	0.15
3	28	3095	78	3.10	1005	72	590	0.29
4	28	3065	82	3.26	815	110	480	0.44
5	24	2950	55	2.60	1095	0	645	0.00
6	24	2915	57	2.67	1015	30	595	0.12
7	24	2860	60	2.76	915	60	540	0.24
8	24	2785	62	2.88	740	90	435	0.36
9	16	2285	28	2.08	835	0	490	0.00
10	16	2245	28	2.09	770	18	455	0.07
11	16	2200	29	2.13	700	35	410	0.14
12	16	2145	30	2.18	565	53	335	0.21

U = Power supply · n = Speed (rpm) · P_{ed} = Power consumption · I = Current draw · qv = Air flow · p_{fs} = Pressure increase

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[A1G200-AH77-52](#)