

AC centrifugal fan

forward-curved, dual-intake
with housing (large flange)



ebm-papst Mulfingen GmbH & Co. KG

Bachmühle 2 · D-74673 Mulfingen

Phone +49 7938 81-0

Fax +49 7938 81-110

info1@de.ebmpapst.com

www.ebmpapst.com

Limited partnership · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRA 590344

General partner Elektrobau Mulfingen GmbH · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRB 590142



Nominal data

Type	D4D225-CC01-02				
Motor	M4D074-LA				
Phase		3~	3~	3~	3~
Nominal voltage	VAC	230	230	400	400
Wiring		Δ	Δ	Y	Y
Frequency	Hz	50	60	50	60
Method of obtaining data		ml	ml	ml	ml
Valid for approval/standard		CE	CE	CE	CE
Speed (rpm)	min ⁻¹	1040	1170	1040	1170
Power consumption	W	660	650	660	650
Current draw	A	2.08	2.08	1.2	1.2
Min. back pressure	Pa	80	200	80	200
Min. back pressure	inH ₂ O	0.32	0.8	0.32	0.8
Min. ambient temperature	°C	-25	-25	-25	-25
Max. ambient temperature	°C	40	40	40	40

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · oe = Customer equipment
Subject to change

Data according to ErP Directive

		Actual	Req. 2015			
01 Overall efficiency η_e	%	46.8	39.5	09 Power consumption P_e	kW	0.31
02 Measurement category		B		09 Air flow q_v	m ³ /h	1505
03 Efficiency category		Total		09 Pressure increase p_f	Pa	350
04 Efficiency grade N		56.3	49	10 Speed (rpm) n	min ⁻¹	1340
05 Variable speed drive		No		11 Specific ratio*		1.00

Data obtained at optimum efficiency level.
The ErP data is determined using a motor-impeller combination in a standardized measurement setup.

* Specific ratio = $1 + p_f / 100\,000\text{ Pa}$

LU-105303



AC centrifugal fan

forward-curved, dual-intake
with housing (large flange)

Technical description


Weight	12.5 kg
Fan size	225 mm
Rotor surface	Painted black
Impeller material	Sheet steel, galvanized
Housing material	Sheet steel, galvanized
Direction of rotation	Counterclockwise, viewed toward rotor
Degree of protection	IP22
Insulation class	"B"
Moisture (F) / Environmental (H) protection class	F2-1
Max. permitted ambient temp. for motor (transport/storage)	+ 80 °C
Min. permitted ambient temp. for motor (transport/storage)	- 40 °C
Installation position	Any
Condensation drainage holes	None
Mode	S1
Motor bearing	Ball bearing
Touch current according to IEC 60990 (measuring circuit Fig. 4, TN system)	< 0.75 mA
With cable	Axial
Protection class	I (with customer connection of protective earth)
Conformity with standards	CE
Approval	CCC; EAC



AC centrifugal fan

forward-curved, dual-intake
with housing (large flange)

Product drawing




1 Cable AWG20, 7x crimped splices

AC centrifugal fan

forward-curved, dual-intake
with housing (large flange)

Connection diagram




	Three-phase motor	Y	Star connection	Δ	Delta connection
L1	black	L2	black	L3	black
V2	black	U2	black	W2	black
PE	green/yellow				



AC centrifugal fan

forward-curved, dual-intake
with housing (large flange)

Curves: Air performance 50 Hz



Measurement: LU-105303-1

Air performance measured according to ISO 5801 installation category A. For detailed information on the measurement setup, contact ebm-papst. Intake sound level: Sound power level according to ISO 13347 / sound pressure level measured at 1 m distance from fan axis. The values given are valid under the specified measuring conditions and may vary due to conditions of installation. For deviations from the standard configuration, the parameters have to be checked on the installed unit.

Measured values

	Wired	U	f	n	P _e	I	qv	p _{fs}	qv	p _{fs}
		V	Hz	min ⁻¹	W	A	m³/h	Pa	CFM	inH2O
1	Y. aus	400	50	1040	660	1.20	3070	80	1805	0.32
2	Y. aus	400	50	1225	473	0.91	2275	260	1340	1.04
3	Y. aus	400	50	1330	323	0.71	1560	340	920	1.36
4	Y. aus	400	50	1385	240	0.63	1000	360	590	1.45


Wired = Wiring · U = Power supply · f = Frequency · n = Speed (rpm) · P_e = Power consumption · I = Current draw · qv = Air flow · p_{fs} = Pressure increase



AC centrifugal fan

forward-curved, dual-intake
with housing (large flange)

Curves: Air performance 60 Hz



Measurement: LU-105306-1

Air performance measured according to ISO 5801 installation category A. For detailed information on the measurement setup, contact ebm-papst. Intake sound level: Sound power level according to ISO 13347 / sound pressure level measured at 1 m distance from fan axis. The values given are valid under the specified measuring conditions and may vary due to conditions of installation. For deviations from the standard configuration, the parameters have to be checked on the installed unit.

Measured values

	Wired	U	f	n	P _e	I	qv	p _{fs}	qv	p _{fs}
		V	Hz	min ⁻¹	W	A	m ³ /h	Pa	CFM	inH ₂ O
1	Y. aus	400	60	1170	650	1.20	2565	200	1510	0.80
2	Y. aus	400	60	1325	554	1.01	2100	325	1235	1.30
3	Y. aus	400	60	1495	415	0.78	1500	425	885	1.71
4	Y. aus	400	60	1590	316	0.64	900	480	530	1.93

Wired = Wiring · U = Power supply · f = Frequency · n = Speed (rpm) · P_e = Power consumption · I = Current draw · qv = Air flow · p_{fs} = Pressure increase



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[D4D225-CC01-02](#)