

D4E225-CC01-48

# AC centrifugal fan

forward-curved, dual-intake  
with housing (large flange)



## ebm-papst Mulfingen GmbH & Co. KG

Bachmühle 2 · D-74673 Mulfingen

Phone +49 7938 81-0

Fax +49 7938 81-110

info1@de.ebmpapst.com

www.ebmpapst.com

Limited partnership · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRA 590344

General partner Elektrobau Mulfingen GmbH · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRB 590142

## Nominal data

|                             |                    |         |         |
|-----------------------------|--------------------|---------|---------|
| Type                        | D4E225-CC01-48     |         |         |
| Motor                       | M4E074-LA          |         |         |
| Phase                       |                    | 1~      | 1~      |
| Nominal voltage             | VAC                | 230     | 230     |
| Frequency                   | Hz                 | 50      | 60      |
| Method of obtaining data    |                    | ml      | ml      |
| Valid for approval/standard |                    | -       | -       |
| Speed (rpm)                 | min <sup>-1</sup>  | 1150    | 1300    |
| Power consumption           | W                  | 650     | 625     |
| Current draw                | A                  | 2.84    | 2.75    |
| Capacitor                   | µF                 | 25      | 16      |
| Capacitor voltage           | VDB                | 400     | 400     |
| Capacitor standard          |                    | S2 (CE) | S2 (CE) |
| Min. back pressure          | Pa                 | 100     | 300     |
| Min. back pressure          | inH <sub>2</sub> O | 0.4     | 1.2     |
| Min. ambient temperature    | °C                 | -25     | -25     |
| Max. ambient temperature    | °C                 | 50      | 50      |
| Starting current            | A                  | 4.5     |         |

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment  
Subject to change



# AC centrifugal fan

forward-curved, dual-intake  
with housing (large flange)

## Technical description


|                                                                            |                                                       |
|----------------------------------------------------------------------------|-------------------------------------------------------|
| Weight                                                                     | 13 kg                                                 |
| Fan size                                                                   | 225 mm                                                |
| Rotor surface                                                              | Painted black                                         |
| Impeller material                                                          | Sheet steel, galvanized                               |
| Housing material                                                           | Sheet steel, galvanized                               |
| Motor suspension                                                           | Motor vibration-damped on both sides                  |
| Direction of rotation                                                      | Counterclockwise, viewed toward rotor                 |
| Degree of protection                                                       | IP22                                                  |
| Insulation class                                                           | "F"                                                   |
| Moisture (F) / Environmental (H) protection class                          | F2-1                                                  |
| Max. permitted ambient temp. for motor (transport/storage)                 | + 80 °C                                               |
| Min. permitted ambient temp. for motor (transport/storage)                 | - 40 °C                                               |
| Installation position                                                      | Any                                                   |
| Condensation drainage holes                                                | None                                                  |
| Mode                                                                       | S1                                                    |
| Motor bearing                                                              | Ball bearing                                          |
| Touch current according to IEC 60990 (measuring circuit Fig. 4, TN system) | < 0.75 mA                                             |
| Motor protection                                                           | Thermal overload protector (TOP) internally connected |
| With cable                                                                 | Axial                                                 |
| Protection class                                                           | I (with customer connection of protective earth)      |
| Approval                                                                   | CSA C22.2 No. 100; UL 1004-1                          |



# AC centrifugal fan


forward-curved, dual-intake  
with housing (large flange)

## Product drawing



1 Cable PFA AWG20 (green/yellow AWG18), 4x crimped splices

## Connection diagram




|    |              |   |       |    |       |
|----|--------------|---|-------|----|-------|
| U1 | blue         | Z | brown | U2 | black |
| PE | green/yellow |   |       |    |       |

# AC centrifugal fan

forward-curved, dual-intake  
with housing (large flange)

## Curves: Air performance 50 Hz



Measurement: LU-35314-1

Air performance measured according to ISO 5801 installation category A. For detailed information on the measurement setup, contact ebm-papst. Intake sound level: Sound power level according to ISO 13347 / sound pressure level measured at 1 m distance from fan axis. The values given are valid under the specified measuring conditions and may vary due to conditions of installation. For deviations from the standard configuration, the parameters have to be checked on the installed unit.

## Measured values

|   | U   | f  | n                 | P <sub>e</sub> | I    | q <sub>V</sub> | p <sub>fs</sub> | q <sub>V</sub> | p <sub>fs</sub>    |
|---|-----|----|-------------------|----------------|------|----------------|-----------------|----------------|--------------------|
|   | V   | Hz | min <sup>-1</sup> | W              | A    | m³/h           | Pa              | cfm            | inH <sub>2</sub> O |
| 1 | 230 | 50 | 1150              | 783            | 3.42 | 2975           | 100             | 1750           | 0.40               |
| 2 | 230 | 50 | 1195              | 689            | 3.05 | 2700           | 200             | 1590           | 0.80               |
| 3 | 230 | 50 | 1300              | 581            | 2.65 | 2215           | 300             | 1305           | 1.20               |
| 4 | 230 | 50 | 1395              | 445            | 2.15 | 1300           | 360             | 765            | 1.45               |


U = Power supply · f = Frequency · n = Speed (rpm) · P<sub>e</sub> = Power consumption · I = Current draw · q<sub>V</sub> = Air flow · p<sub>fs</sub> = Pressure increase



# AC centrifugal fan

forward-curved, dual-intake  
with housing (large flange)

## Curves: Air performance 60 Hz



Measurement: LU-35316-1

Air performance measured according to ISO 5801 installation category A. For detailed information on the measurement setup, contact ebm-papst. Intake sound level: Sound power level according to ISO 13347 / sound pressure level measured at 1 m distance from fan axis. The values given are valid under the specified measuring conditions and may vary due to conditions of installation. For deviations from the standard configuration, the parameters have to be checked on the installed unit.

## Measured values

|   | U   | f  | n                 | P <sub>e</sub> | I    | q <sub>v</sub> | p <sub>ts</sub> | q <sub>v</sub> | p <sub>ts</sub>    |
|---|-----|----|-------------------|----------------|------|----------------|-----------------|----------------|--------------------|
|   | V   | Hz | min <sup>-1</sup> | W              | A    | m³/h           | Pa              | cfm            | inH <sub>2</sub> O |
| 1 | 230 | 60 | 1300              | 625            | 2.75 | 1995           | 300             | 1175           | 1.20               |
| 2 | 230 | 60 | 1465              | 553            | 2.43 | 1700           | 400             | 1000           | 1.61               |
| 3 | 230 | 60 | 1565              | 474            | 2.13 | 1340           | 450             | 790            | 1.81               |
| 4 | 230 | 60 | 1645              | 390            | 1.83 | 800            | 490             | 470            | 1.97               |

U = Power supply · f = Frequency · n = Speed (rpm) · P<sub>e</sub> = Power consumption · I = Current draw · q<sub>v</sub> = Air flow · p<sub>ts</sub> = Pressure increase



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[D4E225-CC01-48](#)