

**ebm-papst Mulfingen GmbH & Co. KG**

Bachmühle 2 · D-74673 Mulfingen

Phone +49 7938 81-0

Fax +49 7938 81-110

info1@de.ebmpapst.com

www.ebmpapst.com

Limited partnership · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRA 590344

General partner Elektrobau Mulfingen GmbH · Headquarters Mulfingen

Amtsgericht (court of registration) Stuttgart · HRB 590142

Nominal data

Type	W1G180-AB47-01	
Motor	M1G074-BF	
Nominal voltage	VDC	48
Nominal voltage range	VDC	36 .. 57
Frequency	Hz	-
Method of obtaining data		fa
Speed (rpm)	min ⁻¹	4600
Power consumption	W	95
Current draw	A	2.30
Max. back pressure	Pa	380
Max. back pressure	inH ₂ O	1.53
Min. ambient temperature	°C	-25
Max. ambient temperature	°C	60

ml = Max. load · me = Max. efficiency · fa = Free air · cs = Customer specification · ce = Customer equipment

Subject to change



Technical description

Weight	1.8 kg
Fan size	180 mm
Rotor surface	Thick-film passivated
Impeller material	PA plastic
Fan housing material	Die-cast aluminum, painted black
Number of blades	5
Airflow direction	"V"
Direction of rotation	Counterclockwise, viewed toward rotor
Degree of protection	IP20
Insulation class	"B"
Moisture (F) / Environmental (H) protection class	H0 - dry environment
Max. permitted ambient temp. for motor (transport/storage)	+80 °C
Min. permitted ambient temp. for motor (transport/storage)	-40 °C
Installation position	Any
Condensation drainage holes	None
Mode	S1
Motor bearing	Ball bearing
Technical features	- Control input 0-10 VDC / PWM - Tach output - Motor current limitation - Soft start
EMC immunity to interference	According to EN 61000-6-2 (industrial environment)
EMC interference emission	According to EN 55022 (Class B)
Motor protection	Reverse polarity and locked-rotor protection
With cable	Lateral
Conformity with standards	EN 60950-1
Approval	CCC; UL 507; EAC; CSA C22.2 No. 113

Technical drawing of the 1000mm x 1000mm cable tray, showing top, side, and detail views with dimensions.

Top View:

- Overall dimensions: 1000mm x 1000mm (indicated by diagonal lines).
- Outer diameter: $\varnothing 220$
- Inner diameter: $\varnothing 208$
- Section line A-A is shown.
- Angle of 45° is indicated for the side flange.
- Angle of 90° is indicated for the top flange.
- Dimension 147.1 is shown for the distance from the center to the mounting hole.

Side View:

- Overall height: 70 ± 0.2
- Flange thickness: 2.5 ± 0.2
- Inner diameter: $\varnothing 169.7 \pm 1$
- Outer diameter: $\varnothing 200 \pm 1$
- Direction of assembly is indicated by an arrow.

Detail A-A:

- Dimensions: $\varnothing 4.3 \pm 0.15$, 12 ± 0.3 , 12 ± 0.3 .

Detail 1:


- Dimensions: 85 ± 10 , 400 ± 20 , 6 .

Detail 2:

- Dimensions: 85 ± 10 , 400 ± 20 , 6 .


- | | |
|---|----------------------------------|
| 1 | Cable AWG 20, 4x crimped splices |
| 2 | Airflow direction "V" |

Connection diagram



No.	Conn.	Designation	Color	Function/assignment
1	1	Un +48 VDC	red	Power supply 48 VDC, maximum ripple 3.5%
1	2	0-10 VDC	yellow	Control input Re > 100k
1	3	Tach	white	Tach output, 3 pulses per revolution, Isink max = 10 mA
1	4	GND	blue	Reference ground

Curves: Air performance


 $\rho = 1.15 \text{ kg/m}^3 \pm 2 \%$

Measurement: LU-50668-1

Measurement: LU-50667-1

Measurement: LU-50670-1

Air performance measured according to ISO 5801 installation category A. For detailed information on the measurement setup, contact ebm-papst. Intake sound level: Sound power level according to ISO 13347 / sound pressure level measured at 1 m distance from fan axis. The values given are valid under the specified measuring conditions and may vary due to conditions of installation. For deviations from the standard configuration, the parameters have to be checked on the installed unit.

Measured values

	U	n	P _{ed}	I	q _v	p _{fs}	q _v	p _{fs}
	V	min ⁻¹	W	A	m ³ /h	Pa	cfm	inH ₂ O
1	57	5170	134	2.65	1035	0	610	0.00
2	57	4980	141	2.83	905	125	535	0.50
3	57	4800	147	2.96	750	243	440	0.98
4	57	5000	141	2.81	455	369	265	1.48
5	48	4600	95	2.30	925	0	545	0.00
6	48	4505	106	2.47	815	100	480	0.40
7	48	4370	112	2.63	680	200	400	0.80
8	48	4555	105	2.45	405	300	240	1.20
9	36	3900	60	1.89	770	0	455	0.00
10	36	3780	64	2.00	680	71	400	0.29
11	36	3685	67	2.10	565	139	335	0.56
12	36	3820	63	1.96	340	207	200	0.83

U = Power supply · n = Speed (rpm) · P_{ed} = Power consumption · I = Current draw · q_v = Air flow · p_{fs} = Pressure increase



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[W1G180-AB47-01](#)