



ECS-P2 (2.5V) and ECS-P3 (3.3V) low jitter, low current Frequency Configurable SMD crystal controlled oscillators.

ECSpresCON™ ECX-P LVPECL Oscillator

Request a Sample



OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS

Parameters	Conditions	ECS-P2 (+2.5V)			ECS-P3 (+3.3V)			Units
		MIN	TYP	MAX	MIN	TYP	MAX	
Frequency Range		10.000		1500.0	10.000		1500.0	MHz
Operating Temperature	Standard	0		+70	0		+70	°C
	Extended (N Option)	-40		+85	-40		+85	°C
Storage Temperature		-55		+125	-55		+125	°C
Supply Voltage	V _{DD}	+2.375	+2.5	+2.625	+3.135	+3.3	+3.465	VDC
Frequency Stability *	Option A			±100			±100	ppm
	Option B			±50			±50	ppm
	Option C			±25			±25	ppm
	Option D			±20			±20	ppm
Input Current	10.0 ~ 100.0 MHz			46			48	mA
	100.1 ~ 250.0 MHz			48			50	mA
	250.1 ~ 500 MHz			53			55	mA
	500.1 ~ 1500.0 MHz			65			68	mA
Output Symmetry	@ 50% V _{DD} level			48/52			48/52	%
Output Load	Differential							
Output Enable	Pin 1 **	0.7%			0.7%			Vdd
Output Disable	Pin 1			0.3%			0.3%	Vdd
Disable Current			16		16			mA
Output Enable Time				200			200	ns
Output Disable Time	Pin 1 = VIL			50			50	ns
"0" Level	VOL	Vdd-1.85V		Vdd-1.6V	Vdd-1.85V		Vdd-1.6V	V
"1" Level	VOH	Vdd-1.03V		Vdd-0.6V	Vdd-1.03V		Vdd-0.6V	V
Rise and Fall Times	10% V _{DD} to 90% Level	150		250	150		250	ps
Aging	@ +25°C (first year)			±2			±2	PPM
Start-up Time	@ +25°C (first year)			10			10	ms
Phase Jitter, rms	12 KHz to 20 MHz band		1.0			1.0		pS
Absolute Voltage Range				+3.63			+3.63	VDC
Moisture Sensitivity Level				1				
Termination Finish				Au				
ESD Sensitivity	Human Body Model			3kV Max.				

*Note: Inclusive of 25°C tolerance, operating temperature, input voltage change, load change, shock and vibration.

**Note: Internal pull-up resistor active output if pin 1 is left open.

Part Numbering Guide: Example ECX-P35BN-156.250

Series	Voltage	Package Size (mm)	Stability	Operating Temperature	Frequency
ECX-P (LVPECL Output)	2 = +2.5V 3 = +3.3V	2 = 2.5 x 2 3 = 3.2 x 2.5 5 = 5 x 3.25 7 = 7 x 5	A = ± 100 ppm B = ± 50 ppm C = ± 25 ppm D = ± 20 ppm	L = -10 ~ +70°C M = -20 ~ +70°C N = -40 ~ +85°C P = -40 ~ +105°C	Customer Specified

Phase Noise and Jitter Data (typical)

SSB Phase Noise Data (dBc/Hz typical)	Frequency (offset)	77.760	122.880	125.000	156.250	212.5	491.520	622.080	1000	1250
	10 Hz	-64	-68	-63	-55	-62	-61	-48	-52	-42
	100 Hz	-84	-99	-94	-85	-93	-86	-85	-82	-81
	1 KHz	-118	-113	-113	-109	-105	-100	-101	-93	-93
	10 KHz	-128	-119	-118	-116	-113	-105	-102	-97	-96
	100 KHz	-137	-120	-119	-118	-115	-105	-103	-97	-97
	1 MHz	-145	-140	-137	-139	-135	-126	-124	-116	-119
	5 MHz	-152	-142	-146	-146	-143	-137	-133	-127	-129
Phase Jitter pS 12 KHz ~ 20 MHz, RMS	0.9	0.8	1.1	0.9	1.0	1.1	1.2	1.5	1.1	

Phase Noise Plot of ECX-H35BM-77.760 (typical)



Package Data	
Item	Description
Lid	Metal
Base	Ceramic
Plating	Gold/Nickel Surface/Under

Dimensions (mm)

7 = 7x5 Package



Figure 1) Top, Side, Bottom & Land

5 = 5x3.2 Package



Figure 2) Top, Side, Bottom & Land

3 = 3.2x2.5 Package



Figure 3) Top, Side, Bottom & Land

2 = 2.5x2 Package



Figure 4) Top, Side, Bottom & Land

Suggested Reflow Profile



Pin Connections	
Pin #	Function
1	O/E or No Connect
2	No Connect
3	Ground
4	Differential Output
5	Complementary Output
6	Supply Voltage

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ECS:

[ECX-P37BN-100.000](#) [ECX-P37BN-150.000](#) [ECX-P37BN-156.2500](#) [ECX-P37BN-250.000](#) [ECX-P37BN-106.250](#)
[ECX-P35BN-250.000](#) [ECX-P37BN-212.500](#) [ECX-P35BN-125.000](#) [ECX-P35BN-100.000](#) [ECX-P35CM-1000.000](#) [ECX-](#)
[P37BN-74.250](#) [ECX-P35CM-150.000](#) [ECX-P37BN-125.000](#) [ECX-P37BN-200.000](#) [ECX-P37CM-125.000](#) [ECX-](#)
[P37CM-62.500](#) [ECX-P37BN-30.000](#) [ECX-P37CM-27.000](#) [ECX-P37CM-1000.000](#) [ECX-P35CM-200.000](#) [ECX-P35BN-](#)
[212.500](#) [ECX-P37CN-100.000](#) [ECX-P37CM-212.500](#) [ECX-P37BN-155.520](#) [ECX-P37BN-500.000](#) [ECX-P35CM-](#)
[125.000](#) [ECX-P37CM-156.250](#) [ECX-P35CM-156.250](#) [ECX-P35CM-500.000](#) [ECX-P37BN-156.250](#) [ECX-P37CM-](#)
[622.080](#) [ECX-P37CM-106.250](#) [ECX-P37CM-200.000](#) [ECX-P37CM-40.000](#) [ECX-P37CM-100.000](#) [ECX-P37CM-](#)
[500.000](#) [ECX-P35BN-156.250](#) [ECX-P35AN-139.246](#) [ECX-P35DM-125.000](#) [ECX-P37AM-156.250](#) [ECX-P37AN-](#)
[250.000](#) [ECX-P27AM-133.000](#) [ECX-P37AM-240.000](#) [ECX-P37CM-644.5312](#) [ECX-P37CN-914.000](#) [ECX-P37DM-](#)
[132.8125](#) [ECX-P37CM-1216.000](#) [ECX-P37CN-1000.025](#) [ECX-P37DM-804.000](#) [ECX-P37DM-622.080](#) [ECX-P37CN-](#)
[850.000](#) [ECX-P37CN-895.000](#) [ECX-P37DM-904.000](#) [ECX-P37DM-1000.000](#) [ECX-P37DM-312.500](#) [ECX-P37CN-](#)
[312.500](#) [ECX-P37BM-622.080](#) [ECX-P37CN-1000.000](#) [ECX-P37CN-282.624](#) [ECX-P37DM-300.000](#) [ECX-P37CM-](#)
[1120.000](#) [ECX-P37BM-800.000](#) [ECX-P37CN-337.500](#) [ECX-P37DM-999.900](#) [ECX-P37BM-400.000](#) [ECX-P37BP-](#)
[1000.000](#) [ECX-P37DM-321.7625](#) [ECX-P37DM-400.000](#) [ECX-P37DM-166.6286](#) [ECX-P37BM-280.000](#) [ECX-P37BM-](#)
[933.120](#) [ECX-P37CN-875.000](#) [ECX-P37DM-74.250](#) [ECX-P35AM-1100.000](#) [ECX-P37CN-865.000](#) [ECX-P37CN-](#)
[906.000](#) [ECX-P37CN-1100.000](#) [ECX-P37CN-220.000](#) [ECX-P37CN-700.000](#) [ECX-P37CN-1216.500](#) [ECX-P37BM-](#)
[900.000](#) [ECX-P37CN-1252.500](#) [ECX-P37CN-500.000](#) [ECX-P37BM-804.000](#) [ECX-P37CN-1000.500](#) [ECX-P37CN-](#)
[1250.000](#) [ECX-P37DM-180.000](#) [ECX-P35CN-1100.000](#) [ECX-P35DM-1250.000](#) [ECX-P37AN-666.670](#) [ECX-P37DM-](#)
[148.500](#) [ECX-P37AM-1000.000](#) [ECX-P37BM-450.000](#) [ECX-P35BM-535.000](#) [ECX-P37AN-282.600](#) [ECX-P37BN-](#)
[1330.000](#) [ECX-P37CN-300.000](#) [ECX-P35DM-1000.000](#) [ECX-P37DM-156.250](#) [ECX-P37DM-212.500](#)