

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	Updated drawing spec.	7/15/22	DK

ELECTRICAL SPECIFICATIONS

Frequency: 50.000 MHz

Frequency Tolerance (@ +25°C): ±7 ppm Max.

Frequency Stability (-10 ~ +70°C): ±10 ppm Max.

Crystal Cut: AT Strip

Load Capacitance (CL): 19 pF

Recommended Drive Level: 100 µW Max.

Effective Series Resistance: 15 Ω Max.

Shunt Capacitance: 5 pF Max.

Aging (@ +25°C, First Year): ±1 ppm Max.

Mode of Operation: Fundamental

Insulation Resistance: 500MΩ Min.

Operating Temperature: -10 ~ +70°C

Storage Temperature: -55 ~ +125°C

Package Type: ECX-53 (5.0x3.2mm)

DIMENSIONS (mm)




Figure 1) Top, Side and Bottom Views

ECS Part Number: ECS-500-CDX-2166



ECS INC. INTERNATIONAL

15351 W. 109th Street

Lenexa, KS 66219

(913) 782-7787

SIGNATURES	DATE	TITLE		
DRN AJ	3/9/2021	50.000 MHz 19 pF SMD Crystal ±7/10 ppm -10 ~ +70°C RoHS		
CHK DK	3/9/2021			
APP BS	3/9/2021			
		SIZE A	DWG NO. ECS-500-CDX-2166	REV A
Dimensions in mm		CAGE CODE: 1G8B7	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ECS:

[ECS-500-CDX-2166](#)