




The ECS-2100 Series clock oscillator offers low current drain and is compatible with HCMOS/TTL logic. The metal package with pin #4 case ground acts as a shielding to minimize radiation.

FEATURES

- HCMOS/TTL logic compatible
- Wide frequency range
- Low power consumption
- Resistance weld package
- 3.3V operation (optional)

PART NUMBERING GUIDE

PART NUMBER *	FREQUENCY STABILITY
ECS-2100A	±100 PPM
ECS-2100B	±50 PPM
ECS-2100C	±25 PPM

* Complete part number to include frequency. i.e. ECS-2100A-100 (100 = 10.000MHz)

OPERATING CONDITIONS/ELECTRICAL CHARACTERISTICS

PARAMETERS	FREQUENCY RANGE	CONDITIONS	MINIMUM	TYPICAL	MAXIMUM	UNITS
FREQUENCY RANGE (f_0)	1.000 ~ 150.000		1.000		150.000	MHz
OPERATING TEMP. RANGE (T_{OPR})	1.000 ~ 150.000		0		+70	°C
STORAGE TEMP. RANGE (T_{STG})	1.000 ~ 150.000		-55		+125	°C
FREQUENCY STABILITY	1.000 ~ 150.000	All conditions*	-100		+100	PPM
INPUT CURRENT (I_{DD})	1.000 ~ 25.000			17	25	mA
	25.000 ~ 50.000			33	46	mA
	50.000 ~ 80.000			45	77	mA
	80.000 ~ 150.000			67	82	mA
OUTPUT SYMMETRY	1.000 ~ 80.000	50% V_{DD} level	45	50 ±3	55	%
	80.000 ~ 150.000	50% V_{DD} level	40	50 ±3	60	%
RISE TIME (T_R)	1.000 ~ 150.000	10% ~ 90% V_{DD} level			5	nS
FALL TIME (T_F)	1.000 ~ 150.000	90% ~ 10% V_{DD} level			5	nS
OUTPUT VOLTAGE (V_{OL}) (V_{OH})	1.000 ~ 150.000	$I_{OL} = 16$ mA			0.5	V
	1.000 ~ 150.000	$I_{OH} = -16$ mA	4.5			V
OUTPUT CURRENT (I_{OL}) (I_{OH})	1.000 ~ 100.000	$V_{OL} = 0.5$ V			16	mA
	1.000 ~ 150.000	$V_{OH} = 4.5$ V			-16	mA
OUTPUT LOAD	1.000 ~ 150.000	TTL			10	pF
	1.000 ~ 80.000	HCMOS			50	pF
	80.000 ~ 150.000	HCMOS			30	pF
START-UP TIME (T_S)	1.000 ~ 150.000	0.0V TO 5.0V			10	mS
SUPPLY VOLTAGE (V_{DC})		+5.0 ±0.25				V _{DC}

* Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock and vibration.

PACKAGE DIMENSIONS (mm)




Figure 1) ECS-2100 Series - Side, Bottom and Top views




Figure 2) TTL Output Wave Form




Figure 3) HCMOS Output Wave Form

PIN CONNECTIONS	
#1	NC
#4	GROUND
#5	OUTPUT
#8	+5V DC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ECS:

[ECS-2100A-350](#) [ECS-2100A-2.4576MHZ](#) [ECS-2100A-8.0MHZ](#) [ECS-2100A-11.0592MHZ](#) [ECS-2103A-300](#) [ECS-2100A-25.0MHZ](#) [ECS-2100A-4.9152MHZ](#) [ECS-2100A-9.216MHZ](#) [ECS-2100A-5.0MHZ](#) [ECS-2100A-14.7456MHZ](#) [ECS-2100A-1.2288MHZ](#) [ECS-2100A-64.0MHZ](#) [ECS-2103A-120](#) [ECS-2100A-28.322MHZ](#) [ECS-2100A-32.514MHZ](#) [ECS-2100A-18.0MHZ](#) [ECS-2100A-8.192MHZ](#) [ECS-2100AX-48.0MHZ](#) [ECS-2100A-4.0MHZ](#) [ECS-2100A-10.0MHZ](#) [ECS-2100A-50.0MHZ](#) [ECS-2100A-24.0MHZ](#) [ECS-2100A-19.6608MHZ](#) [ECS-2100A-400](#) [ECS-2100A-100](#) [ECS-2100A-250](#) [ECS-2100A-240](#) [ECS-2100A-160](#) [ECS-2100A-080](#) [ECS-2100A-320](#) [ECS-2100A-200](#) [ECS-2100A-061](#) [ECS-2100A-120](#) [ECS-2100A-300](#) [ECS-2100A-184](#) [ECS-2100A-073.2](#) [ECS-2100A-162.5](#) [ECS-2100A-110.5](#) [ECS-2100A-480](#) [ECS-2100A-180](#) [ECS-2100A-325.1](#) [ECS-2100A-036](#) [ECS-2100A-035](#) [ECS-2100A-283.2](#) [ECS-2100A-020](#) [ECS-2100A-018](#) [ECS-2100A-051](#) [ECS-2100A-640](#) [ECS-2100A-010](#) [ECS-2100A-040](#) [ECS-2100A-050](#) [ECS-2100A-196.6](#) [ECS-2100A-049](#) [ECS-2100A-060](#) [ECS-2100A-092.1](#) [ECS-2100A-098.3](#) [ECS-2100A-143](#) [ECS-2100A-251.7](#) [ECS-2100A-666](#) [ECS-2100A-012.2](#) [ECS-2100A-024](#) [ECS-2100A-500](#)