





TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	1



SPECIFICATION:

MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING

HOUSING: PA46 BLACK

SPRING: SUS

MAGNET: N52

ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 5V

RATED CURRENT (PER CONTACT): 1A

WORKING STROKE & FORCE: PRESS STROKE 1.3MM (PER CONTACT): 85gf MAX.

LIFE TEST: PRESS STROKE 0.8MM, 10,000 CYCLES MIN.

WORKING TEMPERATURE RANGE: -30~+85° C.




THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

MAGNETIC SPRING LOADED CONNECTOR, 8POS, MALE		ACAD REFERENCE NO.: 685A0811221113E		UNIT: MM	
		DRAWN: J.L.	DATE: 4/6/2023		
		CHECKED: R.S.M	DATE: 4/6/2023		
 <div>EDAC INC TORONTO, ONTARIO CANADA</div> <div>YOUR CONNECTION TO QUALITY & SERVICE</div>		SCALE: (IN CAD 1:1)		SHEET 1 OF 1	
		DRAWING NUMBER: 685A0811221113E			ISSUE 1
		PART NUMBER: 685A0811221113E			
		THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

685A0811221113E