



TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①



SPECIFICATION:

MATERIAL:

CONTACT: BRASS, GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING
HOUSING: PA46, BLACK
MAGNET: N52

ELECTRICAL CHARACTERISTICS:

RATED VOLTAGE (PER CONTACT): 12V
RATED CURRENT (PER CONTACT): 2A
INSULATION RESISTANCE: 100MEGAOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: 100V AT 60Hz
CONTACT RESISTANCE: 30mOHMS MAX. BEFORE TEST AND 60mOHMS MAX. AFTER TEST
SALT SPRAY TEST: 5% SALT SPRAY CONCENTRATION, TEMPERATURE 35°C,
TEST TIME 24 HOURS, NO CORROSION
WORKING TEMPERATURE RANGE: -30~+85°C.



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

MAGNETIC SPRING LOADED CONNECTOR, 14POS, FEMALE

ACAD REFERENCE NO.: 686B1421260123E		UNIT: MM
DRAWN: J.L.	DATE: 4/20/2023	
CHECKED: R.S.M	DATE: 4/20/2023	
SCALE: (IN CAD 1:1)	SHEET 1 OF 1	
DRAWING NUMBER: 686B1421260123E	ISSUE	
PART NUMBER: 686B1421260123E	1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

686B1421260123E