

TOLERANCE
UNLESS OTHERWISE
SPECIFIED

| | |
|------|--------|
| .X | ±0.3 |
| .XX | ±0.20 |
| .XXX | ±0.100 |

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER

ORIGINAL

1

NOTE:

NO COPPER WIRE OR DEFORMATION AFTER STAMPING







MATERIAL: PHOSPHOR BRONZE C5191, HARDNESS 190-210HV

WIRE SIZE: AWG 22-30, OD: 1.50 MAX

PLATING: TIN FLASH OVER NICKEL (NICKEL 30U" MIN, TIN FLASH 80U" MIN)

PACKAGING: 10K PCS/REEL, 100K PCS/BOX. BOX SIZE: 46X46X26 CM

| WIRE RANGE | INSULATION O.D. | MATERIAL | FINISH | QTY/REEL |
|------------|-----------------|-----------------|--------|-----------|
| AWG#24-30 | 1.50mm (max) | PHOSPHOR BRONZE | | 10,000pcs |



MEASURING
POINT (BACK)



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

2.0mm CRIMP STYLE CONNECTOR

ACAD REFERENCE NO.: 140-941-290

DRAWN: P.M.

DATE: OCT. 27/2020

CHECKED: C.B.

DATE: OCT. 27/2020

SCALE: N.T.S.

SHEET 1 OF 1

DRAWING NUMBER: 140-941-290

ISSUE

PART NUMBER: 140-941-290

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

140-941-290