




THIS IS A CAD GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①
PART NUMBER TABLE ADDED AND LEAD REMOVE FROM PLATING	②
F.BRIONES AUG.30/06	
OPERATING TEMP (WAS 125°)	
J.LEE SEPT 21/09	③
BENDING NOTE ADDED	
F.BRIONES JUL. 10/13	④

CARD SLOT ACCEPTS .054 (1.37) TO .070 (1.78) THICK P.C. BOARD



MATERIALS:

INSULATOR: THERMOPLASTIC POLYESTER
UL94V-0, COLOR (SEE TABLE)

CONTACTS: COPPER, NICKEL, TIN ALLOY CA-725
GOLD ON CONTACT AREA, TIN ON TAIL OVER NICKEL UNDERPLATE.

SPECIFICATIONS:

- 1- CURRENT RATING: 3 AMPERES.
- 2- CONTACT RESISTANCE: 10 MILLIOHMS MAXIMUM.
- 3- INSULATION RESISTANCE: 5,000 MEGOHMS MINIMUM.
- 4- DIELECTRIC WITHSTANDING VOLTAGE: 1,200 VAC RMS AT SEA LEVEL.
- 5- INSERTION AND WITHDRAWAL FORCES: 16oz AND 1oz RESPECTIVELY PER CONTACT PAIR
- 6- OPERATING TEMPERATURE: -65°C TO +105°C

CONNECTOR PART NUMBER	INSULATOR COLOR
342-008-559-201	GREEN
392-008-559-201	BLACK

CONTACTS POSITION AFTER BENDING SHALL BE BETWEEN ±2° FROM CENTER LINE BUT PARALLEL WITH OTHER CONTACTS.

TITLE		ACAD REFERENCE NO.	
392 SERIES R/A CONNECTOR		392-008-559-201	
DRAWN: F.JAWDI		DATE: JUNE 17/02	
PART NUMBER		SEE TABLE	
DRAWING NUMBER		ISSUE	
392-008-559-201		4	



EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC. AND SHALL NOT BE REPRODUCED OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EDAC:](#)

[392-008-559-201](tel:392-008-559-201)