

Mounting Option .116 (2.95) I.D. Floating Eyelets

Contact Detail 90 Degree Bend (Code 522 and 540 Contacts)
.156 [3.96] Contact Spacing x .200 [5.08] Row Spacing

Technical drawing of a 90-degree bend contact strip. The drawing shows a side view of the strip with two rows of contacts. The top row of contacts is labeled with a dimension of 5.000 [127.00] for the length of the contact array. The bottom row of contacts is labeled with a dimension of 5.432 [137.97] for the total length of the strip, including the mounting eyelets. The contact spacing is .156 [3.96] and the row spacing is .200 [5.08]. The mounting eyelets are labeled with a dimension of 0.500 [12.70] for the height of the mounting flange. The overall height of the strip is 0.116 (2.95) I.D. Floating Eyelets.

Mounting Option .116 (2.95) I.D. Floating Eyelets

Contact Detail 90 Degree Bend (Code 522 and 540 Contacts)
.156 [3.96] Contact Spacing x .200 [5.08] Row Spacing

Technical drawing of a 90-degree bend contact strip. The drawing shows a side view of the strip with two rows of contacts. The top row of contacts is labeled with a dimension of 5.000 [127.00] for the length of the contact array. The bottom row of contacts is labeled with a dimension of 5.432 [137.97] for the total length of the strip, including the mounting eyelets. The contact spacing is .156 [3.96] and the row spacing is .200 [5.08]. The mounting eyelets are labeled with a dimension of 0.500 [12.70] for the height of the mounting flange. The overall height of the strip is 0.116 (2.95) I.D. Floating Eyelets.

Mounting Option .116 (2.95) I.D. Floating Eyelets

Contact Detail 90 Degree Bend (Code 522 and 540 Contacts)
.156 [3.96] Contact Spacing x .200 [5.08] Row Spacing

Technical drawing of a 90-degree bend contact strip. The drawing shows a side view of the strip with two rows of contacts. The top row of contacts is labeled with a dimension of 5.000 [127.00] for the length of the contact array. The bottom row of contacts is labeled with a dimension of 5.432 [137.97] for the total length of the strip, including the mounting eyelets. The contact spacing is .156 [3.96] and the row spacing is .200 [5.08]. The mounting eyelets are labeled with a dimension of 0.500 [12.70] for the height of the mounting flange. The overall height of the strip is 0.116 (2.95) I.D. Floating Eyelets.

Mounting Option .116 (2.95) I.D. Floating Eyelets


Contact Detail 90 Degree Bend (Code 522 and 540 Contacts)
.156 [3.96] Contact Spacing x .200 [5.08] Row Spacing

Technical drawing of a 90-degree bend contact strip. The drawing shows a side view of the strip with two circular mounting eyelets at the ends. The strip has a total length of 5.432 [137.97] and a total width of 0.500 [12.70]. The contact area is 5.000 [127.00] long and .156 [3.96] wide. The contact spacing is .156 [3.96] and the row spacing is .200 [5.08]. The strip is bent 90 degrees at the ends, with a 90-degree bend detail shown at the ends. The mounting eyelets have an inner diameter of .116 (2.95).

Mounting Option .116 (2.95) I.D. Floating Eyelets

Contact Detail 90 Degree Bend (Code 522 and 540 Contacts)
.156 [3.96] Contact Spacing x .200 [5.08] Row Spacing

Technical drawing of a 90-degree bend contact strip. The drawing shows a side view of the strip with two circular mounting eyelets at the ends. The strip has a total length of 5.432 [137.97] and a total width of 0.500 [12.70]. The contact area is 5.000 [127.00] long and .156 [3.96] wide. The contact spacing is .156 [3.96] and the row spacing is .200 [5.08]. The strip is bent 90 degrees at the ends, with a 90-degree bend detail shown at the ends. The mounting eyelets have an inner diameter (I.D.) of .116 (2.95).



- **Contact Bend Details**
- **Mounting Options**

Part Number: 307-062-559-203



YOUR CONNECTION TO QUALITY & SERVICE

YOUR CONNECTION TO QUALITY & SERVICE

DRAWN: J.LEE	DATE: AUG. 11/09
--------------	------------------

SCALE: NTS	SHEET 1 OF 3
------------	--------------

307 Assembly	1
--------------	---

307 Assembly

1

Single Row Contacts - Read One Side of Daughter Board

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER

ORIGINAL



558 Contact Code



559 Contact Code

Single Row Contacts - Read Both Sides of Daughter Board



553 Contact Code



554 Contact Code



557 Contact Code

Dual Row Contacts - Read Both Sides of Daughter Board



555 Contact Code



556 Contact Code

0.240 [6.10] Up to 27/54 Pin
0.162 [4.11] 28/56 and Over



558 Contact Code

0.240 [6.10] Up to 27/54 Pin
0.162 [4.11] 28/56 and Over
0.290 [7.37] Up to 27/54 Pin
.212 [5.38] 28/56 and Over



559 Contact Code



560 Contact Code

307/ 357 Series Card Edge Connector Contact Bend Detail



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 307 ENG MASTER

DRAWN: J.LEE DATE: AUG. 11/09

CHECKED: DATE:

SCALE: NTS SHEET 2 OF 3

DRAWING NUMBER ISSUE

307 Assembly

1

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER



ISSUE NUMBER

ORIGINAL



Code x01



Code x12

.128 [3.25] Dia
Through Holes



Code x02

.128 [3.25] Dia
Through Holes



Code x03



Code x04

.156 [3.96] Dia
Through Holes



Code x07

M3-0.5 Metric
Threaded Insert



Code x08

#4-40 UNC
Threaded Insert



Code x58



Code x68



Code x78

307 / 357 Card Edge Connector Mounting Options



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 307 ENG MASTER

DRAWN: J.LEE

DATE: AUG. 11/09

CHECKED:

DATE:

SCALE: NTS

SHEET 3 OF 3

DRAWING NUMBER

307 Assembly

ISSUE

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

[307-062-559-203](tel:307-062-559-203)