




345/395 SERIES

Card Edge Connector 0.100" (2.54mm) Pitch



FEATURES:

- .100" (2.54mm) Contact Spacing x .200" (5.08mm) Row Spacing
- Accepts .062" (1.57mm) Nominal Thickness P.C. Board
- High Profile Insulator Body, .600" (15.24mm)
- Contact Termination Options include P.C. Tail, Wire Wrap, 90 Degree Bends and Extender Board Bends
- Single or Dual Row Configurations
- Large Variety of Mounting Options, Flush or Offset Lugs
- Accepts between Contact and In-Contact Polarizing Keys
- Pre-assembled Card Guides are available
- Automatic Wire Wrap Positioning Holes
- RoHS Compliant & UL Certified

Specifications:

Insulator Material	UL 94V-0 Thermoplastic Polyester
Contact Material	Copper Alloy
Contact Plating	Gold Plating on mating area and Tin Plating on tails with Nickel underplating all over
Current Rating	3 Amperes
Contact Resistance	10 milliohms maximum
Dielectric Withstand Voltage	1200 VAC rms at sea level between adjacent contacts
Insulation Resistance	5000 Megaohms minimum
Operating Temperature	-40°C to +105°C
Insertion Force	16oz (4.45N) maximum per contact pair when tested with .070" (1.78mm) thick gauge
Withdrawal Force	1oz (0.28N) minimum per contact pair when tested with .054" (1.37mm) thick gauge

Example Part Number: **345-050-520-202**

Series _____
Total Number of Contacts _____
Contact Code _____
Contact Rows and Insulator Style _____
Mounting Options _____

Series:

345
395

Insulator Color

Thermoplastic Polyester, Green
Thermoplastic Polyester, Black

Total Number of Contacts:

005, 006, 072
010, 012, 144

Contact Rows

Single Row
Dual Row

Contact Rows & Insulator Style

Description

1	Single Row, Flush Mounting Lugs
2	Dual Row, Flush Mounting Lugs
4	Single Row, .110 (2.79) Offset Lugs
5	Dual Row, .110 (2.79) Offset Lugs
6	Single Row, .170 (4.32) Offset Lugs
8	Dual Row, .170 (4.32) Offset Lugs

Contact Code

Description & Tail Size

Tail Length "G"

500	Wire Hole	.050 x .025 (1.27 x 0.64)	.260 (6.60)
520	P.C. Tail	.030 x .018 (0.76 x 0.46)	.175 (4.45)
521	P.C. Tail	.025 Square (0.64 Square)	.150 (3.81)
523	P.C. Tail	.025 Square (0.64 Square)	.390 (9.91)
524	P.C. Tail	.018 Square (0.46 Square)	.175 (4.45)
525	P.C. Tail	.018 Square (0.46 Square)	.150 (3.81)
540	Wire Wrap	.025 Square (0.64 Square)	.560 (14.22)
541	Wire Wrap	.025 Square (0.64 Square)	.750 (19.05)
542	Wire Wrap	.025 Square (0.64 Square)	.645 (16.38)
544	Wire Wrap	.050 x .025 (1.27 x 0.64)	.750 (19.05)
555	EXTENDER BOARD BEND (CODE 500 CONTACTS)		
556	EXTENDER BOARD BEND (CODE 520 CONTACTS)		
558	90 DEGREE BEND (CODE 541 CONTACTS)		
559	90 DEGREE BEND (CODE 541 CONTACTS)		
560	EXTENDER BOARD BEND (CODE 523 CONTACTS)		

Mounting Options:

Description

01	No Mounting Lug
02	Ø.128" (Ø3.25mm) Mounting Holes
03	Ø.116" (Ø2.95mm) I.D. Floating Eyelets
04	Ø.156" (Ø3.96mm) Mounting Holes
07	M3-0.5 Metric Threaded Inserts
08	#4-40 Unified Threaded Inserts
12	Ø.128" (Ø3.25mm) Side Mounting Holes
58	.468" (11.89mm) Offset Card Guides
78	In-Line Card Guides 2.750" (69.85mm) Long
88	In-Line Card Guides 1.250" (31.75mm) Long

Ordering Code Notes:

- 1) All connector sizes up to 72 contacts single row / 144 contacts dual row are available upon request.
- 2) The 500 contact code is only available in the 345 series. Green polyphenylene sulphide insulator material will be supplied.
- 3) For details of the extender board and 90 degree bends refer to next pages.
- 4) For lug-less connectors, code 01 mounting, specify contact row code 1 or 2.
- 5) For details of the mounting options refer to page 3 & page 4.


www.edac.net



345/395 SERIES



Card Edge Connector 0.100" (2.54mm) Pitch






NUMBER OF CONTACTS		"A"±.015 (±0.38)		"B"±.010 (±0.25)		"C"±.015 (±0.38)		"D"+.010 /-.006 (+0.25/-0.15)		"E"±.005 (±0.13)	
Single	Double	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm
5	10	1.335	33.91	1.075	27.31	0.760	19.30	0.600	15.24	0.400	10.16
10	20	1.835	46.61	1.575	40.01	1.260	32.00	1.100	27.94	0.900	22.86
13	26	2.135	54.23	1.875	47.63	1.560	39.62	1.400	35.56	1.200	30.48
15	30	2.335	59.31	2.075	52.71	1.760	44.70	1.600	40.64	1.400	35.56
18	36	2.635	66.93	2.375	60.33	2.060	52.32	1.900	48.26	1.700	43.18
22	44	3.035	77.09	2.775	70.49	2.460	62.48	2.300	58.42	2.100	53.34
25	50	3.335	84.71	3.075	78.11	2.760	70.10	2.600	66.04	2.400	60.96
30	60	3.835	97.41	3.575	90.81	3.260	82.80	3.100	78.74	2.900	73.66
31	62	3.935	99.95	3.675	93.35	3.360	85.34	3.200	81.28	3.000	76.20
36	72	4.435	112.65	4.175	106.05	3.860	98.04	3.700	93.98	3.500	88.90
43	86	5.135	130.43	4.875	123.83	4.560	115.82	4.400	111.76	4.200	106.68
50	100	5.835	148.21	5.575	141.61	5.260	133.60	5.100	129.54	4.900	124.46
60	120	6.835	173.61	6.575	167.01	6.260	159.00	6.100	154.94	5.900	149.86
72	144	8.035	204.09	7.775	197.49	7.460	189.48	7.300	185.42	7.100	180.34



345/395 SERIES

Card Edge Connector 0.100" (2.54mm) Pitch





Card Edge Connector 0.100" (2.54mm) Pitch

CONTACT CODE 558

CONTACT CODE 559


CONTACT CODE 555 BEND USES
WIRE HOLE CONTACTS

CONTACT CODE 556


CONTACT CODE 560

MTG. OPTION	A	B
555	0.245(6.22)	
556	0.170(4.32)	
558	0.235(5.97)	0.635(16.13)
559	0.285(7.24)	0.635(16.13)
560	0.375(9.53)	

IN-CONTACT
POLARIZING KEY
P/N 345-240-328



BETWEEN CONTACT
POLARIZING KEY
P/N 345-240-318



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

[345-028-523-508](#) [345-028-523-512](#) [345-028-523-407](#) [345-028-523-408](#) [345-028-523-412](#) [345-028-523-458](#) [345-028-523-478](#) [345-028-523-488](#) [345-028-523-258](#) [345-028-523-278](#) [345-028-523-288](#) [345-028-523-402](#) [345-028-523-403](#) [345-028-523-404](#) [345-028-523-202](#) [345-028-523-203](#) [345-028-523-204](#) [345-028-523-207](#) [345-028-523-208](#) [345-028-523-212](#) [345-028-523-107](#) [345-028-523-108](#) [345-028-523-112](#) [345-028-523-158](#) [345-028-523-178](#) [345-028-523-188](#) [345-028-521-878](#) [345-028-521-888](#) [345-028-523-101](#) [345-028-523-102](#) [345-028-523-103](#) [345-028-523-104](#) [345-028-521-803](#) [345-028-521-804](#) [345-028-521-807](#) [345-028-521-808](#) [345-028-521-812](#) [345-028-521-858](#) [345-028-521-608](#) [345-028-521-612](#) [345-028-521-658](#) [345-028-521-678](#) [345-028-521-688](#) [345-028-521-802](#) [345-028-521-578](#) [345-028-521-588](#) [345-028-521-602](#) [345-028-521-603](#) [345-028-521-604](#) [345-028-521-607](#) [345-028-521-503](#) [345-028-521-504](#) [345-028-521-507](#) [345-028-521-508](#) [345-028-521-512](#) [345-028-521-558](#) [345-028-521-408](#) [345-028-521-412](#) [345-028-521-458](#) [345-028-521-478](#) [345-028-521-488](#) [345-028-521-502](#) [345-028-521-278](#) [345-028-521-288](#) [345-028-521-402](#) [345-028-521-403](#) [345-028-521-404](#) [345-028-521-407](#) [345-028-521-203](#) [345-028-521-204](#) [345-028-521-207](#) [345-028-521-208](#) [345-028-521-212](#) [345-028-521-258](#) [345-028-521-107](#) [345-028-521-108](#) [345-028-521-112](#) [345-028-521-158](#) [345-028-521-178](#) [345-028-521-188](#) [345-028-520-878](#) [345-028-520-888](#) [345-028-521-101](#) [345-028-521-102](#) [345-028-521-103](#) [345-028-521-104](#) [345-028-520-803](#) [345-028-520-804](#) [345-028-520-807](#) [345-028-520-808](#) [345-028-520-812](#) [345-028-520-858](#) [345-028-520-608](#) [345-028-520-612](#) [345-028-520-658](#) [345-028-520-678](#) [345-028-520-688](#) [345-028-520-802](#) [345-028-520-578](#) [345-028-520-588](#)