



CRYSTAL OSCILLATOR (SPXO)

OUTPUT : CMOS

SG-210 S*B

- Frequency range : 2 MHz to 60 MHz
- Supply voltage : 1.5 V Typ. / 1.8 V Typ. / 2.5 V Typ. / 3.3 V Typ.
- Current consumption : 0.9 mA Typ.
(SEB: 1.8 V No load condition 48 MHz)
- Function : Standby($\overline{\text{ST}}$)
- External dimensions : 2.5 × 2.0 × 0.8 mm
- Operation temperature : +105 °C / +125 °C



Product Number (please contact us)
Q33210Bx0xxxx00



Actual size



Specifications (characteristics)

Item	Symbol	SG-210SGB	SG-210SEB	SG-210SDB	SG-210SCB	Conditions / Remarks	
Output frequency range	f ₀	2 MHz to 32 MHz	2 MHz to 60 MHz			Please contact us about available frequencies	
Supply voltage	V _{CC}	1.5 V Typ. 1.3 V to 1.7 V	1.8 V Typ. 1.6 V to 2.2 V	2.5 V Typ. 2.2 V to 3.0 V	3.3 V Typ. 2.7 V to 3.6 V		
Storage temperature	T _{stg}	-40 °C to +125 °C				Storage as single product.	
Operating temperature	T _{use}	-40 °C to +85 °C / -40 °C to +105 °C / -40 °C to +125 °C					
Frequency tolerance	f _{tol}	F: ±20 × 10 ⁻⁶				-10 °C to +60 °C, f ₀ ≤ 32 MHz, V _{CC} ±10%, except reflow drift.	
		B: ±50 × 10 ⁻⁶ , C: ±100 × 10 ⁻⁶				-20 °C to +70 °C	
		L:±50 × 10 ⁻⁶ ,M:±100 × 10 ⁻⁶				-40 °C to +85 °C	
		—	Y:±50 × 10 ⁻⁶ ,W:±100 × 10 ⁻⁶			-40 °C to +105 °C	
		—	Z:±100 × 10 ⁻⁶ ,X:±150 × 10 ⁻⁶			-40 °C to +125 °C	
Current consumption	I _{CC}	1.0 mA Max.	1.6 mA Max.	2.4 mA Max.	3.0 mA Max.	No load condition	
		—	2.0 mA Max.	3.0 mA Max.	4.0 mA Max.	No load condition +105 °C,+125 °C	
Stand-by current	I _{std}	0.3 µA Max.	0.5 µA Max.	1.0 µA Max.	1.0 µA Max.	ST =GND	
		—	1.6 µA Max.	2.4 µA Max.	3.0 µA Max.	ST =GND +105 °C,+125 °C	
Symmetry	SYM	45 % to 55 %	45 % to 55 %	45 % to 55 %	45 % to 55 %	2 MHz≤f ₀ ≤16 MHz	50 % V _{CC} level L _{CMOS} ≤ 15 pF
		40 % to 60 %				16 MHz<f ₀ ≤32 MHz	
		—				32 MHz<f ₀ ≤60 MHz	
		—				+105 °C,+125 °C	
Output voltage	V _{OH}	90 % V _{CC} Min.				I _{OH} =-1 mA	
	V _{OL}	10 % V _{CC} Max.				I _{OL} = 1 mA	
Output load condition(CMOS)	L _{CMOS}	15 pF Max.					
Input voltage	V _{IH}	80 % V _{CC} Min.				ST terminal	
	V _{IL}	20 % V _{CC} Max.					
Rise time and Fall time	tr/ tr	5 ns Max.	4 ns Max.	3 ns Max.		+85 °C	20 % V _{CC} to 80 % V _{CC} level,L _{CMOS} =15 pF
		—	7 ns Max			+105 °C,+125 °C	
Start-up time	t _{str}	3 ms Max.				t=0 at 90 % V _{CC} (+105 °C,+125 °C : 5 ms Max.)	
Frequency aging	f _{aging}	±3 × 10 ⁻⁶ / year Max.				+25 °C, First year, V _{CC} =1.5 V,1.8 V, 2.5 V, 3.3 V	

Product Name
(Standard form)

SG-210 S G B 27.000000MHz L

① ② ③ ④ ⑤

① Model ② Function (S: Standby)

③ Supply voltage ④ Frequency


⑤ Frequency tolerance

③ Supply voltage	
G	1.5 V Typ.
E	1.8 V Typ.
D	2.5 V Typ.
C	3.3 V Typ.

⑤ Frequency tolerance		*Except for SGB
F	$\pm 20 \times 10^{-6}$	-10 to +60 °C ($f_0 \leq 32$ MHz)
B	$\pm 50 \times 10^{-6}$	-20 to +70 °C
C	$\pm 100 \times 10^{-6}$	-20 to +70 °C
L	$\pm 50 \times 10^{-6}$	-40 to +85 °C
M	$\pm 100 \times 10^{-6}$	-40 to +85 °C
Y*	$\pm 50 \times 10^{-6}$	-40 to +105 °C
W*	$\pm 100 \times 10^{-6}$	-40 to +105 °C
Z*	$\pm 100 \times 10^{-6}$	-40 to +125 °C
X*	$\pm 150 \times 10^{-6}$	-40 to +125 °C


External dimensions

(Unit:mm)



Footprint (Recommended)

(Unit:mm)



PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.

WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs,

Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired ISO/TS 16949 certification that is requested strongly by major automotive manufacturers as standard.

ISO/TS16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

► Explanation of the mark that are using it for the catalog

	► Pb free.
	► Complies with EU RoHS directive. *About the products without the Pb-free mark. Contains Pb in products exempted by EU RoHS directive. (Contains Pb in sealing glass, high melting temperature type solder or other.)
	► Designed for automotive applications such as Car Multimedia, Body Electronics, Remote Keyless Entry etc.
	► Designed for automotive applications related to driving safety (Engine Control Unit, Air Bag, ESC etc).

Notice

- This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
- The information about applied circuitry, software, usage, etc. written in this material is intended for reference only. Seiko Epson does not assume any liability for the occurrence of infringing on any patent or copyright of a third party. This material does not authorize the licensing for any patent or intellectual copyrights.
- When exporting the products or technology described in this material, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that you would not make the products available to any third party who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
 - / Space equipment (artificial satellites, rockets, etc.) / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.) / Medical instruments to sustain life / Submarine transmitters / Power stations and related / Fire work equipment and security equipment / traffic control equipment / and others requiring equivalent reliability.
- All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Epson:

[SG-210SCB 19.2000MF0](#) [SG-210SCB 25.0000ML3](#) [SG-210SEB 19.2000MC3](#) [SG-210SEB 26.0000MC0](#) [SG-210SEB 26.0000ML3](#) [SG-210SEB 26.0000MM0](#) [SG-210SEB 27.0000MF3](#) [SG-210SEB 38.4000MB0](#) [SG-210SEB 26.0000MF3](#) [SG-210SGB 25.0000ML](#) [SG-210SCB 8.0000MY](#) [SG-210SEB 19.2000MF0](#) [SG-210SEB 19.2000MF3](#) [SG-210SEB 25.0000ML](#) [SG-210SEB 26.0000MB](#) [SG-210SEB 26.0000MF](#) [SG-210SEB 26.0000MF0](#) [SG-210SEB 26.0000MM3](#) [SG-210SEB 27.0000ML](#) [SG-210SEB 30.0000MC](#) [SG-210SEB 30.0000MF](#) [SG-210SEB 40.0000MW3](#) [SG-210SEB 48.0000MC](#) [SG-210SGB 16.0000MC](#) [SG-210SGB 19.2000ML3](#) [SG-210SGB 25.0000ML0](#) [SG-210SGB 25.0000ML3](#) [SG-210SDB 25.0000MBX](#) [SG-210SDB 25.6000MBX](#) [SG-210SDB 48.0000MBX](#) [SG-210SDB 48.0000MCX](#) [SG-210SEB 10.2400MM0](#) [SG-210SEB 14.7456MLX](#) [SG-210SEB 27.0000MZX](#) [SG-210SEB 30.0000MCX](#) [SG-210SEB 40.0000MFX](#) [SG-210SEB 40.0000MY0](#) [SG-210SEB 40.0000MY3](#) [SG-210SEB 6.1440MLX](#) [SG-210SDD 62.5000ML3](#) [SG-210SEB 12.2880MB0](#) [SG-210SEB 14.7456ML3](#) [SG-210SEB 19.2000MC](#) [SG-210SCB 14.0000MLX](#) [SG-210SCB 14.0000MYX](#) [SG-210SCB 16.0000MLX](#) [SG-210SCB 19.0000MYX](#) [SG-210SCB 19.2000MFX](#) [SG-210SCB 24.0000MBX](#) [SG-210SCB 25.0000MBX](#) [SG-210SCB 25.0000MYX](#) [SG-210SCB 27.0000MZX](#) [SG-210SCB 50.0000MLX](#) [SG-210SCB 50.0000MZ5](#) [SG-210SCB 40.0000MM3](#) [SG-210SDB 48.0000ML3](#) [SG-210SCB 50.0000ML](#) [SG-210SEB 27.0000MF0](#) [SG-210SDB 16.0000MF0](#) [SG-210SCB 25.6000MY3](#) [SG-210SCB 26.2144MW3](#) [SG-210SCB-16-000M-M](#)