

**CRYSTAL OSCILLATOR (SPXO)****OUTPUT : CMOS****Low Jitter****SG-210S\*H**

- Frequency range : 80.000 MHz to 170.000 MHz  
Fundamental mode oscillator
- Supply voltage : 1.8 V Typ. / 2.5 V Typ. / 3.3 V Typ.
- Output : CMOS
- Function : Standby( $\overline{ST}$ )
- External dimensions : 2.5 × 2.0 × 0.8 mm




Product Number (please contact us)

SG-210SCH: X1G003931xxxx00

SG-210SDH: X1G003941xxxx00

SG-210SEH: X1G003951xxxx00



Actual size

**Specifications (characteristics)**

Item	Symbol	Specifications			Conditions / Remarks	
		SG-210SEH	SG-210SDH	SG-210SCH		
Output frequency range	fo	80.000 MHz to 170.000 MHz			Please contact us about available frequencies.	
		100MHz, 106.25MHz, 125MHz, 133.33MHz, 150MHz, 156.25MHz			Standard frequency. *1	
Supply voltage	Vcc	1.8 V ± 10%	2.5 V ± 10%	3.3 V ± 10%	*2	
Storage temperature	T_stg	-40 °C to +125 °C			Storage as single product.	
Operating temperature	T_use	-40 °C to +85 °C				
Frequency tolerance	f_tol	B: ±50 × 10 <sup>-6</sup> , C: ±100 × 10 <sup>-6</sup>			-20 °C to +70 °C	
		L: ±50 × 10 <sup>-6</sup> , M: ±100 × 10 <sup>-6</sup>			-40 °C to +85 °C	
Current consumption	Icc	6.0 mA Max.	7.0 mA Max.	9.0 mA Max.	No load condition,80 MHz≤fo≤125 MHz	
		8.0 mA Max.	9.0 mA Max.	11.0 mA Max.	No load condition,125 MHz<fo≤170 MHz	
Stand-by current	I_std	10.0 µA Max.			ST =GND	
Symmetry	SYM	45 % to 55 %			50 % Vcc level, L_CMOS ≤ 15 pF	
Output voltage	VOH	90 % Vcc Min.			IOH = -4mA	
	VOL	10 % Vcc Max.			IOL = 4mA	
Output load condition (CMOS)	L_CMOS	15 pF Max.				
Input voltage	VIH	80 % Vcc Min.			ST terminal	
	VIL	20 % Vcc Max.				
Rise time / Fall time	tr/ tr	3 ns Max.	2 ns Max.		20 % Vcc to 80 % Vcc level, L_CMOS ≤15 pF	
Start-up time	t_str	5 ms Max.			T=0 at 90 % Vcc	
Frequency aging	f_aging	±5 × 10 <sup>-6</sup> / year Max.			+25 °C, First year	
Jitter *3	tp-p	22 ps Typ.	20 ps Typ.		Peak to Peak	L_CMOS ≤ 15 pF
Phase Jitter	tpJ	0.7 ps Max.	0.6 ps Max.		Offset frequency: 12kHz to 20MHz	

\*1 Please contact us for requirements not listed in the specification.

\*2  $f_0 \geq 157$  MHz:  $V_{CC} \pm 5\%$ 

\*3 Based on SIA-3100C signal integrity analyzer made from WAVECREST.

Product Name  
(Standard form)

SG-210 S E H 125.000000MHz L

① ② ③ ④ ⑤

① Model ② Function (S: Standby) ③ Supply voltage

④ Frequency ⑤ Frequency tolerance

③ Supply voltage

E 1.8 V Typ.


D 2.5 V Typ.

C 3.3 V Typ.


⑤ Frequency tolerance

B  $\pm 50 \times 10^{-6}$  / -20 to +70 °CC  $\pm 100 \times 10^{-6}$  / -20 to +70 °CL  $\pm 50 \times 10^{-6}$  / -40 to +85 °CM  $\pm 100 \times 10^{-6}$  / -40 to +85 °C**External dimensions**

(Unit:mm)

**Footprint (Recommended)**

(Unit:mm)



## PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.





## WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs,

Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired ISO/TS 16949 certification that is requested strongly by major automotive manufacturers as standard.

ISO/TS16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

### ► Explanation of the mark that are using it for the catalog

	► Pb free.
	► Complies with EU RoHS directive. *About the products without the Pb-free mark. Contains Pb in products exempted by EU RoHS directive. (Contains Pb in sealing glass, high melting temperature type solder or other.)
	► Designed for automotive applications such as Car Multimedia, Body Electronics, Remote Keyless Entry etc.
	► Designed for automotive applications related to driving safety (Engine Control Unit, Air Bag, ESC etc ).

## Notice

- This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
- The information about applied circuitry, software, usage, etc. written in this material is intended for reference only. Seiko Epson does not assume any liability for the occurrence of infringing on any patent or copyright of a third party. This material does not authorize the licensing for any patent or intellectual copyrights.
- When exporting the products or technology described in this material, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that you would not make the products available to any third party who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
  - / Space equipment (artificial satellites, rockets, etc.) / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.) / Medical instruments to sustain life / Submarine transmitters / Power stations and related / Fire work equipment and security equipment / traffic control equipment / and others requiring equivalent reliability.
- All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Epson:

[SG-210SEH 100.0000ML](#) [SG-210SEH 125.0000ML3](#) [SG-210SEH 150.0000ML](#) [SG-210SEH 150.0000ML3](#) [SG-210SCH 133.0000ML](#) [SG-210SCH 133.3330ML](#) [SG-210SCH 83.3300MLX](#) [SG-210SEH 100.0000ML0](#) [SG-210SEH 100.0000MLX](#) [SG-210SEH 125.0000ML](#) [SG-210SEH 133.3300ML](#) [SG-210SEH 80.0000ML](#) [SG-210SDH 100.0000ML0](#) [SG-210SDH 156.2500ML](#) [SG-210SDH 156.2500ML0](#) [SG-210SDH 156.2500ML3](#) [SG-210SCH 125.0000Mv](#) [SG-210SCH 125.0000ML0](#) [SG-210SCH 125.0000ML](#) [SG-210SCH 133.3300ML](#) [SG-210SCH 125.0000ML5](#) [SG-210SCH 100.0000ML3](#)