


**VC-TCXO/TCXO
HIGH STABILITY**
TG2016SBN / TG2520SBN


- Output frequency : 13 MHz to 55MHz
- Supply voltage : 1.8 V Typ./ 2.8 V Typ./ 3.0 V Typ./ 3.3 V Typ.
- Frequency / temperature characteristics
 - : $\pm 0.5 \times 10^{-6}$ Max. (-40 °C to +85 °C)
 - : $\pm 2.0 \times 10^{-6}$ Max. (-40 °C to +85 °C)
- External dimensions: 2.0 × 1.6 × 0.73 mm / 2.5 × 2.0 × 0.8 mm
- Applications : GPS, RF
Wireless communication devices
(CDMA, WCDMA, LTE, WiMAX, other)
- Features : High stability, Low noise



Product Number (Please contact us)
TG2016SBN : X1G004691xxxxxx
TG2520SBN : X1G005151xxxxxx



TG2016SBN
(2.0 × 1.6 × 0.73 mm)



TG2520SBN
(2.5 × 2.0 × 0.8 mm)

Actual size

TG2016SBN

TG2520SBN

Specifications (characteristics)

Item	Symbol	VC-TCXO	TCXO	Conditions / Remarks
Output frequency range	f ₀	13 MHz to 55MHz 16 MHz, 16.368 MHz, 16.369 MHz, 16.384 MHz, 16.8 MHz, 19.2 MHz, 20 MHz, 26 MHz, 27MHz, 28.974 MHz, 30 MHz, 32 MHz, 37.4 MHz, 38.4 MHz, 39 MHz and 40 MHz		Standard frequency
Supply voltage	V _{CC}	1.8 V ±0.1 V / 2.8 V ±5 % / 3.0 V ±5 % / 3.3 V ±5 %		Supply voltage range :1.7 V to 3.63 V
Storage temperature	T _{stg}	-40 °C to +90 °C		Storage as single product.
Operating temperature	T _{use}	G: -40 °C to +85 °C		
Frequency tolerance	f _{tol}	±1.5 × 10 ⁻⁶ Max.		After reflow, +25 °C
Frequency/temperature characteristics	f ₀ -T _C	C: ±0.5 × 10 ⁻⁶ Max. / G: -40 °C to +85 °C F: ±2.0 × 10 ⁻⁶ Max. / G: -40 °C to +85 °C		Standard stability version
Frequency/load coefficient	f ₀ -Load	±0.1 × 10 ⁻⁶ Max.		10 kΩ // 10 pF ±10 %
Frequency/voltage coefficient	f ₀ -V _{CC}	±0.1 × 10 ⁻⁶ Max.		V _{CC} ± 5 %
Frequency aging	f _{age}	±0.5 × 10 ⁻⁶ Max.		+25 °C, First year, 13 MHz≤ f ₀ ≤20 MHz, 26 MHz≤ f ₀ ≤40 MHz
		±1.5 × 10 ⁻⁶ Max.		+25 °C ,First year, 20 MHz< f ₀ <26 MHz 40 MHz< f ₀ ≤55 MHz
Current consumption	I _{CC}	1.2 mA Max.		13 MHz≤ f ₀ <16 MHz
		1.4 mA Max.		16 MHz≤ f ₀ ≤27 MHz
		1.5 mA Max.		27 MHz< f ₀ ≤36 MHz
		1.8 mA Max.		36 MHz< f ₀ ≤40 MHz
		2.0 mA Max.		40 MHz< f ₀ ≤52 MHz
		2.2 mA Max.		52 MHz< f ₀ ≤55 MHz
Input resistance	R _{in}	500 kΩ Min.	-	V _C - GND (DC)
Frequency control range	f _{cont}	±8.0 × 10 ⁻⁶ to ±12.0 × 10 ⁻⁶	-	B: V _C =0.9 V ±0.6 V (V _{CC} =1.8 V) or C: V _C =1.4 V ±1.0 V (V _{CC} =2.8 V) or D: V _C =1.5 V ±1.0 V (V _{CC} =3.0 V) or E: V _C =1.65 V ±1.0 V (V _{CC} =3.3 V)
Frequency change polarity	-	Positive polarity	-	
Symmetry	SYM	45 % to 55 %		GND level (DC cut)
Output voltage	V _{PP}	0.8 V Min.		Peak to Peak
Start-up time	t _{str}	1.0 ms Max.		T=0 at 90% V _{CC}
Output load condition	Load_R	10 kΩ		DC cut capacitor = 0.01 μF
	Load_C	10 pF		

* Note : Please contact us for requirements not listed in this specification.

Product Name **TG2016 SBN 26.000000MHz** I C G N N M
 (Standard form) ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Model (TG2016, TG2520)

② Output (S: Clipped sine wave) ③ Frequency

④ Supply voltage (Refer to symbol table) ⑤ Frequency / temperature characteristics (C: $\pm 0.5 \times 10^{-6}$ Max., F: $\pm 2.0 \times 10^{-6}$ Max.)


⑥ Operating temperature (G: -40 °C to +85 °C) ⑦ OE function (N: Non) ⑧ Vc function (Refer to symbol table, A: Vc = any)

⑨ Internal identification code ("L", "M", "H" is default)


④ Supply voltage[Vcc], ⑧ Vc function[Vc] (Symbol table)					
Voltage [V]		VC-TCXO			
④ Vcc (Typ.)	T: 1.8 to 3.3	T: 1.8 to 3.3	K: 2.5 to 3.3	P: 2.6 to 3.3	M: 2.8 to 3.3
⑧ Vc (Typ.)	N: Non	B: 0.9	C: 1.4	D: 1.5	E: 1.65

External dimensions

(Unit:mm)


Footprint (Recommended)

(Unit:mm)



PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.





WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs,

Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired ISO/TS 16949 certification that is requested strongly by major automotive manufacturers as standard.

ISO/TS16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

► Explanation of the mark that are using it for the catalog

	► Pb free.
	► Complies with EU RoHS directive. *About the products without the Pb-free mark. Contains Pb in products exempted by EU RoHS directive. (Contains Pb in sealing glass, high melting temperature type solder or other.)
	► Designed for automotive applications such as Car Multimedia, Body Electronics, Remote Keyless Entry etc.
	► Designed for automotive applications related to driving safety (Engine Control Unit, Air Bag, ESC etc).

Notice

- This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
- The information about applied data, circuitry, software, usage, etc. written in this material is intended for reference only. Seiko Epson does not assume any liability for the occurrence of customer damage or infringing on any patent or copyright of a third party. This material does not authorize the licensing for any patent or intellectual copyrights.
- When exporting the products or technology described in this material, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that you would not make the products available to any third party who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
 - / Space equipment (artificial satellites, rockets, etc.) / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.) / Medical instruments to sustain life / Submarine transmitters / Power stations and related / Fire work equipment and security equipment / traffic control equipment / and others requiring equivalent reliability.
- All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Epson:

TG2016SBN 16.0000M-TCGNBM3	TG2016SBN 16.0000M-TCGNNM5	TG2016SBN 16.0000M-KCGNCM3
TG2016SBN 16.0000M-PCGNM0	TG2016SBN 16.0000M-PCGNM3	TG2016SBN 16.3680M-MCGNEM3
TG2016SBN 40.0000M-PCGNM3	TG2016SBN 39.0000M-TCGNNM3	TG2016SBN 40.0000M-TCGNNM0
TG2016SBN 40.0000M-KCGNCM0	TG2016SBN 40.0000M-MCGNEM3	TG2016SBN 40.0000M-TCGNBM0
TG2016SBN 38.4000M-PCGNM0	TG2016SBN 38.4000M-TCGNBM5	TG2016SBN 39.0000M-MCGNEM0
TG2016SBN 38.0000M-MCGNEM5	TG2016SBN 30.0000M-TCGNBM5	TG2016SBN 30.0000M-TCGNNM5
TG2016SBN 32.0000M-TCGNBM0	TG2016SBN 37.4000M-KCGNCM3	TG2016SBN 40.0000M-MCGNEM0
TG2016SBN 28.9740M-TCGNBM3	TG2016SBN 30.0000M-PCGNM3	TG2016SBN 32.0000M-PCGNM5
TG2016SBN 37.4000M-PCGNM5	TG2016SBN 32.0000M-MCGNEM5	TG2016SBN 30.0000M-KCGNCM5
TG2016SBN 16.3840M-MCGNEM5	TG2016SBN 19.2000M-PCGNM0	TG2016SBN 27.0000M-KCGNCM0
TG2016SBN 28.9740M-PCGNM3	TG2016SBN 28.9740M-KCGNCM5	TG2016SBN 28.9740M-MCGNEM5
TG2016SBN 19.2000M-TCGNNM0	TG2016SBN 20.0000M-TCGNBM5	TG2016SBN 26.0000M-MCGNEM0
TG2016SBN 26.0000M-MCGNEM5	TG2016SBN 26.0000M-TCGNBM5	TG2016SBN 16.3840M-MCGNEM0
TG2016SBN 20.0000M-PCGNM3	TG2016SBN 26.0000M-MCGNEM3	TG2016SBN 16.3690M-MCGNEM5
TG2016SBN 16.3840M-TCGNBM0	TG2016SBN 20.0000M-KCGNCM5	TG2016SBN 16.8000M-PCGNM3
TG2016SBN 37.0000M-MCGNEM0	TG2016SBN 37.0000M-MCGNEM5	TG2016SBN 38.4000M-TCGNBM3
TG2016SBN 40.0000M-PCGNM5	TG2016SBN 16.3690M-MCGNEM3	TG2016SBN 16.3840M-TCGNNM5
TG2016SBN 40.0000M-PCGNM0	TG2016SBN 26.0000M-TCGNBM0	TG2016SBN 27.0000M-PCGNM3
TG2016SBN 30.0000M-TCGNBM3	TG2016SBN 32.0000M-MCGNEM3	TG2016SBN 40.0000M-TCGNNM3
TG2016SBN 39.0000M-KCGNCM3	TG2016SBN 30.0000M-MCGNEM3	TG2016SBN 32.0000M-TCGNNM0
TG2016SBN 30.0000M-TCGNNM3	TG2016SBN 32.0000M-PCGNM3	TG2016SBN 37.4000M-TCGNBM5
TG2016SBN 28.9740M-TCGNNM0	TG2016SBN 16.3680M-KCGNCM5	TG2016SBN 20.0000M-KCGNCM3
TG2016SBN 20.0000M-TCGNBM3	TG2016SBN 28.9740M-PCGNM0	TG2016SBN 37.4000M-TCGNBM0
TG2016SBN 28.9740M-TCGNBM0	TG2016SBN 16.3840M-KCGNCM5	TG2016SBN 16.3840M-PCGNM0
TG2016SBN 16.3840M-TCGNNM3	TG2016SBN 19.2000M-MCGNEM0	TG2016SBN 26.0000M-PCGNM5
TG2016SBN 27.0000M-PCGNM0	TG2016SBN 16.0000M-TCGNNM3	TG2016SBN 16.3690M-TCGNNM5
TG2016SBN 20.0000M-TCGNBM0	TG2016SBN 27.0000M-MCGNEM3	TG2016SBN 28.9740M-KCGNCM0
TG2016SBN 19.2000M-MCGNEM3	TG2016SBN 19.2000M-PCGNM3	TG2016SBN 19.2000M-TCGNBM0
TG2016SBN 19.2000M-TCGNNM3	TG2016SBN 20.0000M-PCGNM0	TG2016SBN 26.0000M-TCGNNM5

<u>TG2016SBN 16.3680M-KCGNCM3</u>	<u>TG2016SBN 16.3840M-TCGNBM3</u>	<u>TG2016SBN 16.3840M-TCGNNM0</u>
<u>TG2016SBN 16.8000M-KCGNCM0</u>	<u>TG2016SBN 16.8000M-KCGNCM3</u>	<u>TG2016SBN 16.3680M-TCGNBM0</u>
<u>TG2016SBN 16.3840M-TCGNBM5</u>	<u>TG2016SBN 16.3680M-MCGNEM0</u>	<u>TG2016SBN 16.3690M-PCGNDM3</u>
<u>TG2016SBN 16.3690M-TCGNNM3</u>	<u>TG2016SBN 16.0000M-TCGNBM5</u>	<u>TG2016SBN 16.3680M-TCGNBM5</u>
<u>TG2016SBN 38.4000M-PCGNDM3</u>		