


Eveready 1215

**AA**  
**SUPER HEAVY DUTY**



**Industry Standard Dimensions**



**Chemical System:** Zinc-Manganese Dioxide (Zn/MnO<sub>2</sub>)  
(No Added Mercury or Cadmium)

**Designation:** ANSI-15D, IEC-R6

**Battery Voltage:** 1.5 Volts

**Operating Temp:** -18°C to 55°C (0°F to 130°F)

**Average Weight:** 15.0 grams (0.5 oz.)

**Volume:** 8.0 cubic centimeters (0.5 cubic inch)

**Average Capacity:** 1,100 mAh to 0.8 volts  
(Rated capacity at 25 mA continuous at 21°C)

**Cell:** One No. 15 (size "AA")

**Jacket:** Metal


**INTERNAL RESISTANCE VS. TEMPERATURE**

The measurement is an approximation of the battery's actual internal resistance. It is sensitive to the loads and operator technique.


**Schedule:** Background Load 750 ohms  
Pulse Load 4.0 ohms  
Pulse Duration 1 second

Temperature	Typical Ri (ohms)
45°C (113°F)	0.4
21°C (70°F)	0.5
0°C (32°F)	0.8
-21°C (-4°F)	5.0

**CONSTANT RESISTANCE PERFORMANCE**  
Typical Service



**CONSTANT CURRENT DISCHARGE**  
Typical Service



**Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.


**Contents herein do not constitute a warranty.**

Copyright © Eveready Battery Co. - All rights reserved


# Eveready 1215

## Industry Standard Tests (21° C)


**RADIO**  
43 ohm - 4 hours/day




**RECORDER**  
10 ohm - 1 hr/day



**TOY**  
3.9 ohm - 1 hr/day



**PULSE TEST**  
1.8 ohms - 15sec/min 24 hours/day



**Important Notice**

This data sheet contains information specific to batteries manufactured at the time of its publication.

**Contents herein do not constitute a warranty.**

Copyright © Eveready Battery Co. - All rights reserved

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Energizer:](#)

[1215BP4](#) [1215SW-4](#)