


Electrical Data (电气参数)

Type 类型	Power Rating 额定功率	Operating Temperature 工作温度范围	Max.Working Voltage 最大工作 电压	Max.Overload Voltage 最大过负荷 电压	Dielectric With- standing Voltage 绝缘耐压	Resistance Range 阻值范围		TCR 温度系数
						±0.1% ±0.25%	±0.5% ±1%	
TC02	1/16W	-55℃~+155℃	25V	50V	100V	100Ω~2KΩ	100Ω~2KΩ	±5PPM/℃
						50Ω~12KΩ	50Ω~12KΩ	±10PPM/℃
						10Ω~332KΩ	10Ω~332KΩ	±25PPM/℃
						10Ω~332KΩ	10Ω~332KΩ	±50PPM/℃
TC03	1/10W	-55℃~+155℃	75V	150V	300V	100Ω~4KΩ	100Ω~4KΩ	±5PPM/℃
						10Ω~50KΩ	10Ω~50KΩ	±10PPM/℃
						4.7Ω~1MΩ	1Ω~1MΩ	±25PPM/℃
						4.7Ω~1MΩ	1Ω~1MΩ	±50PPM/℃
TC05	1/8W	-55℃~+155℃	150V	300V	500V	100Ω~15KΩ	100Ω~15KΩ	±5PPM/℃
						10Ω~100KΩ	10Ω~100KΩ	±10PPM/℃
						4.7Ω~2MΩ	1Ω~2MΩ	±25PPM/℃
						4.7Ω~2MΩ	1Ω~2MΩ	±50PPM/℃
TC06	1/4W	-55℃~+155℃	200V	400V	500V	100Ω~15KΩ	100Ω~15KΩ	±5PPM/℃
						10Ω~200KΩ	10Ω~200KΩ	±10PPM/℃
						4.7Ω~3MΩ	1Ω~3MΩ	±25PPM/℃
						4.7Ω~3MΩ	1Ω~3MΩ	±50PPM/℃
TC07	1/3W	-55℃~+155℃	200V	400V	500V	10Ω~1MΩ	10Ω~1MΩ	±10PPM/℃
						4.7Ω~1.5MΩ	2.49Ω~1.5MΩ	±25PPM/℃
						4.7Ω~1.5MΩ	2.49Ω~1.5MΩ	±50PPM/℃
TC10	1/3W	-55℃~+155℃	200V	400V	500V	100Ω~25KΩ	100Ω~25KΩ	±5PPM/℃
	1/2W					50Ω~200KΩ	50Ω~200KΩ	±10PPM/℃
						4.7Ω~3MΩ	1Ω~3MΩ	±25PPM/℃
						4.7Ω~3MΩ	1Ω~3MΩ	±50PPM/℃
TC12	3/4W	-55℃~+155℃	200V	400V	500V	100Ω~25KΩ	100Ω~25KΩ	±5PPM/℃
						50Ω~200KΩ	50Ω~200KΩ	±10PPM/℃
						4.7Ω~3MΩ	1Ω~3MΩ	±25PPM/℃
						4.7Ω~3MΩ	1Ω~3MΩ	±50PPM/℃

Ordering Procedure (Example:Thin Film TC06 1/4W 0.1% 25PPM 1KΩ T/R-5000)

订购方式(例如: 薄膜TC06 1/4W 0.1% 25PPM 1KΩ T/R-5000)



Remark: For more details, please check page 152, Part No. System. 注: 更多细节详见 P152 标准料号系统。

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Royalohm:](#)

<u>TC0310B1001T5C</u>	<u>TC0310B1002T5C</u>	<u>TC0310B1003T5C</u>	<u>TC0310B100JT5C</u>	<u>TC0310B1241T5C</u>	<u>TC0310B1331T5C</u>
<u>TC0310B1500T5C</u>	<u>TC0310B1501T5C</u>	<u>TC0310B1621T5C</u>	<u>TC0310B180JT5C</u>	<u>TC0310B1912T5C</u>	<u>TC0310B2001T5C</u>
<u>TC0310B2002T5C</u>	<u>TC0310B2051T5C</u>	<u>TC0310B2401T5C</u>	<u>TC0310B2491T5C</u>	<u>TC0310B2800T5C</u>	
<u>TC0310B2801T5C</u>	<u>TC0310B3001T5C</u>	<u>TC0310B3012T5C</u>	<u>TC0310B3091T5C</u>	<u>TC0310B3301T5C</u>	<u>TC0310B3302T5C</u>
<u>TC0310B3323T5C</u>	<u>TC0310B3601T5C</u>	<u>TC0310B3602T5C</u>	<u>TC0310B3741T5C</u>	<u>TC0310B3901T5C</u>	
<u>TC0310B4700T5C</u>	<u>TC0310B4701T5C</u>	<u>TC0310B4751T5C</u>	<u>TC0310B4992T5C</u>	<u>TC0310B5100T5C</u>	<u>TC0310B5101T5C</u>
<u>TC0310B510JT5C</u>	<u>TC0310B5230T5C</u>	<u>TC0310B5490T5C</u>	<u>TC0310B5600T5C</u>	<u>TC0310B5601T5C</u>	<u>TC0310B560JT5C</u>
<u>TC0310B6042T5C</u>	<u>TC0310B6200T5C</u>	<u>TC0310B698JT5C</u>	<u>TC0310B7500T5C</u>	<u>TC0310B750JT5C</u>	<u>TC0310B9091T5C</u>
<u>TC0310F1000T5C</u>	<u>TC0310F1001T5C</u>	<u>TC0310F1002T5C</u>	<u>TC0310F1211T5C</u>	<u>TC0310F150JT5C</u>	<u>TC0310F1800T5C</u>
<u>TC0310F1801T5C</u>	<u>TC0310F2201T5C</u>	<u>TC0310F4700T5C</u>	<u>TC0310F4701T5C</u>	<u>TC0310F470JT5C</u>	<u>TC0310F5100T5C</u>
<u>TC0310F510JT5C</u>	<u>TC0315B1502T5C</u>	<u>TC0315B150JT5C</u>	<u>TC0315B2401T5C</u>	<u>TC0315B3322T5C</u>	<u>TC0325B1000T5C</u>
<u>TC0325B1001T5C</u>	<u>TC0325B1002T5C</u>	<u>TC0325B1003T5C</u>	<u>TC0325B1004T5C</u>	<u>TC0325B100JT5C</u>	<u>TC0325B1022T5C</u>
<u>TC0325B1023T5C</u>	<u>TC0325B1051T5C</u>	<u>TC0325B1053T5C</u>	<u>TC0325B1070T5C</u>	<u>TC0325B1072T5C</u>	
<u>TC0325B1073T5C</u>	<u>TC0325B1101T5C</u>	<u>TC0325B1102T5C</u>	<u>TC0325B1103T5C</u>	<u>TC0325B1130T5C</u>	<u>TC0325B1132T5C</u>
<u>TC0325B1150T5C</u>	<u>TC0325B1152T5C</u>	<u>TC0325B115JT5C</u>	<u>TC0325B1181T5C</u>	<u>TC0325B1182T5C</u>	<u>TC0325B1183T5C</u>
<u>TC0325B1200T5C</u>	<u>TC0325B1201T5C</u>	<u>TC0325B1202T5C</u>	<u>TC0325B1203T5C</u>	<u>TC0325B120JT5C</u>	<u>TC0325B1211T5C</u>
<u>TC0325B1212T5C</u>	<u>TC0325B1240T5C</u>	<u>TC0325B1241T5C</u>	<u>TC0325B1242T5C</u>	<u>TC0325B1243T5C</u>	
<u>TC0325B1272T5C</u>	<u>TC0325B1273T5C</u>				