


LOW-JITTER SAW OSCILLATOR (SPSO) OUTPUT : CMOS

EG - 2021 / 2001CA

- Frequency range : 62.5 MHz to 250 MHz
- Supply voltage : 2.5 V ... EG-2021CA
3.3 V ... EG-2001CA
- Output : CMOS
- Function : Output enable (OE)
- External dimensions : 7.0 × 5.0 × 1.2 mm
- Very low jitter and low phase noise by SAW unit.



Product Number (please contact us)
EG-2021CA: Q3807CA00xxxx00
EG-2001CA: Q3801CA00xxxx00



Actual size

EG-2021CA

EG-2001CA

Specifications (characteristics)

Item	Symbol	Specifications		Conditions / Remarks	
		EG-2021CA			EG-2001CA
Output frequency range	f _o	62.500 MHz to 170.000MHz	170.001MHz to 250.000MHz	106.250 MHz to 170.000 MHz	Please contact us about available frequencies.
Supply voltage	V _{cc}	2.5 V± 0.125 V		3.3 V± 0.3 V	
Storage temperature	T _{stg}	-40 °C to +100 °C			Storage as single product.
Operating temperature	T _{use}	P: 0 °C to +70 °C R: -5 °C to +85 °C		0 °C to +70° C	
Frequency tolerance	f _{tol}	G: ± 50 × 10 ⁻⁶ H: ± 100 × 10 ⁻⁶		Z: ± 50 × 10 ⁻⁶ Y,H: ±100 × 10 ⁻⁶	
Current consumption	I _{cc}	25 mA Max.	30 mA Max.	50 mA Max.	OE=V _{cc} , No load condition
Disable current	I _{dis}	600 µA Max.		10 µA Max.	OE=GND
Symmetry	SYM	45 % to 55 %	40 % to 60 %	45 % to 55 %	50 % V _{cc} level, L _{CMOS} ≤ Max.
Output voltage	V _{OH}	V _{cc} -0.35 V Min.		V _{cc} -0.4 V Min.	I _{OH} = -8 mA
	V _{OL}	0.35 V Max.		0.4 V Max.	I _{OL} = 8 mA
Output load condition (CMOS)	L _{CMOS}	15 pF Max.			
Input voltage	V _{IH}	70 % V _{cc} Min.			OE terminal
	V _{IL}	30 % V _{cc} Max.			
Rise time / Fall time	t _r / t _f	2 ns Max.			Between 20% V _{cc} and80% V _{cc} level, L _{CMOS} ≤ Max.
Start-up time	t _{str}	10 ms Max.			Time at minimum supply voltage to be 0 s
Jitter *1	t _{DJ}	0.2 ps Typ.			Deterministic Jitter
	t _{RJ}	3 ps Typ.			Random Jitter
	t _{RMS}	3 ps Typ.			σ (RMS of total distribution)
	t _{p-p}	25 ps Typ.			Peak to Peak
	t _{acc}	4 ps Typ.			Accumulated Jitter(σ) n=2 to 50000 cycles
Phase Jitter	t _{PJ}	1 ps Max.			Offset frequency: 12 kHz to 20 MHz
Frequency aging	f _{aging}	± 10 × 10 ⁻⁶ / year Max.		± 5 × 10 ⁻⁶ / year Max.	+25 °C, First year, V _{cc} =2.5 V,3.3 V

*1 Tested using a DTS-2075 Digital timing system made by WAVECREST with jitter analysis software VISI6.

Product Name **EG-2021 CA 125.000000MHz C H P A** (⑤⑥⑦: GPA, GRA are not available)

(Standard form)

① ② ③ ④⑤⑥⑦

①Model ②Package type ③Frequency

④Output(C:CMOS)

⑤Frequency tolerance ⑥Operating temperature

⑦Frequency aging (A*2: Frequency tolerance include aging, N*3: Frequency tolerance exclude aging)

⑤Frequency tolerance		⑥Operating temp.	
G	±50 × 10 ⁻⁶	P	0 to +70°C
H	±100 × 10 ⁻⁶	R	-5 to +85°C

Product Name **EG-2001 CA 125.000000MHz P C H**

(Standard form)

① ② ③ ④⑤⑥

①Model ②Package type ③Frequency

④Symmetry (P: 50±5%) ⑤Supply voltage

⑥Frequency tolerance / Operating temperature

⑤Supply voltage	
C	3.3 V Typ.

⑥Frequency tolerance / Operating temperature	
H*2	±100 × 10 ⁻⁶ / 0 to +70°C
Y*3	±100 × 10 ⁻⁶ / 0 to +70°C
Z*4	±50 × 10 ⁻⁶ / 0 to +70°C

*2 This includes initial frequency tolerance, temperature variation, supply voltage variation, load variation, reflow drift, and aging(+25 °C,10 years).



*3 This includes initial frequency tolerance, temperature variation, supply voltage variation, load variation, and reflow drift.(except aging)

*4 This includes initial frequency tolerance, and temperature variation.(except reflow drift, supply voltage variation, load variation and aging)

External dimensions

(Unit:mm)

Footprint (Recommended) (Unit:mm)



PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.

WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs,

Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired ISO/TS 16949 certification that is requested strongly by major automotive manufacturers as standard.

ISO/TS16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

► Explanation of the mark that are using it for the catalog

	► Pb free.
	► Complies with EU RoHS directive. *About the products without the Pb-free mark. Contains Pb in products exempted by EU RoHS directive. (Contains Pb in sealing glass, high melting temperature type solder or other.)
	► Designed for automotive applications such as Car Multimedia, Body Electronics, Remote Keyless Entry etc.
	► Designed for automotive applications related to driving safety (Engine Control Unit, Air Bag, ESC etc).

Notice

- This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Seiko Epson.
- The information about applied circuitry, software, usage, etc. written in this material is intended for reference only. Seiko Epson does not assume any liability for the occurrence of infringing on any patent or copyright of a third party. This material does not authorize the licensing for any patent or intellectual copyrights.
- When exporting the products or technology described in this material, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of weapon of mass destruction or for other military purposes. You are also requested that you would not make the products available to any third party who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require extremely high reliability, such as the applications stated below, you must obtain permission from Seiko Epson in advance.
 - / Space equipment (artificial satellites, rockets, etc.) / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.) / Medical instruments to sustain life / Submarine transmitters / Power stations and related / Fire work equipment and security equipment / traffic control equipment / and others requiring equivalent reliability.
- All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Epson:

[EG-2001CA 106.2500M-PCHB](#) [EG-2001CA 106.2500M-PCHL0](#) [EG-2001CA 125.0000M-PCHL0](#) [EG-2001CA 133.0000M-PCHB](#) [EG-2001CA 133.0000M-PCHL3](#) [EG-2001CA 133.3333M-PCHB](#) [EG-2001CA 150.0000M-PCHB](#) [EG-2001CA 156.2500M-PCHB](#) [EG-2001CA 166.0000M-PCZB](#) [EG-2021CA 100.0000M-CGPNB](#) [EG-2021CA 125.0000M-CGPNB](#) [EG-2021CA 125.0000M-CGPNL3](#) [EG-2021CA 150.0000M-CGRNB](#) [EG-2021CA 150.0000M-CHPNB](#) [EG-2021CA 166.0000M-CHPNB](#) [EG-2001CA 106.2500M-PCHL3](#) [EG-2001CA 125.0000M-PCHL3](#) [EG-2001CA 106.2500M-PCZL3](#) [EG-2001CA 125.0000M-PCHB](#) [EG-2001CA 125.0000M-PCZL0](#) [EG-2001CA 125.0000M-PCZL3](#) [EG-2001CA 133.0000M-PCZL0](#) [EG-2001CA 133.3333M-PCHL0](#) [EG-2001CA 160.0000M-PCHL3](#) [EG-2001CA 125.0000M-PCHS](#) [EG-2021CA 75.0000M-CHPAB](#) [EG-2021CA 174.7031M-CHTAB](#) [EG-2021CA 250.0000M-CGPNB](#) [EG-2021CA 62.5000M-CGPNB](#) [EG-2021CA 62.5000M-CHPAB](#) [EG-2021CA 62.5000M-CHPAL3](#) [EG-2021CA 75.0000M-CGPNB](#) [EG-2021CA 125.0000M-CHRNB](#) [EG-2021CA 133.0000M-CGPNB](#) [EG-2021CA 133.0000M-CGPNL3](#) [EG-2021CA 133.0000M-CHPNB](#) [EG-2021CA 133.0000M-CHPNL3](#) [EG-2021CA 150.0000M-CGPNB](#) [EG-2021CA 100.0000M-CHPAB](#) [EG-2021CA 100.0000M-CHPAL0](#) [EG-2021CA 100.0000M-CHPAL3](#) [EG-2021CA 100.0000M-CHPNB](#) [EG-2021CA 125.0000M-CHPAB](#) [EG-2021CA 125.0000M-CHPAL3](#) [EG-2001CA 161.1328M-PCZB](#) [EG-2001CA 166.0000M-PCHB](#) [EG-2001CA 166.0000M-PCHL0](#) [EG-2001CA 166.0000M-PCHL3](#) [EG-2001CA 166.0000M-PCZL3](#) [EG-2001CA 166.6667M-PCHB](#) [EG-2001CA 156.2500M-PCHL3](#) [EG-2001CA 156.2500M-PCZB](#) [EG-2001CA 159.3750M-PCHB](#) [EG-2001CA 160.0000M-PCHB](#) [EG-2001CA 160.0000M-PCZB](#) [EG-2001CA 161.1328M-PCHB](#) [EG-2001CA 150.0000M-PCZL0](#) [EG-2001CA 150.0000M-PCZL3](#) [EG-2001CA 155.5200M-PCHB](#) [EG-2001CA 155.5200M-PCHL3](#) [EG-2001CA 155.5200M-PCZB](#) [EG-2001CA 156.2500M-PCHL0](#) [EG-2001CA 133.3333M-PCZB](#) [EG-2001CA 135.0000M-PCZB](#) [EG-2001CA 143.0000M-PCHB](#) [EG-2001CA 143.0000M-PCZB](#) [EG-2001CA 150.0000M-PCHL3](#) [EG-2001CA 150.0000M-PCZB](#) [EG-2001CA 132.8125M-PCHB](#) [EG-2001CA 132.8125M-PCZB](#) [EG-2001CA 133.0000M-PCYL0](#) [EG-2001CA 133.0000M-PCZB](#) [EG-2001CA 133.0000M-PCZL3](#) [EG-2001CA 133.3333M-PCHL3](#) [EG-2001CA 106.2500M-PCZB](#) [EG-2001CA 106.2500M-PCZL0](#) [EG-2001CA 108.0000M-PCHB](#) [EG-2001CA 125.0000M-PCYB](#) [EG-2001CA 125.0000M-PCZB](#) [EG-2001CA 128.0000M-PCHB](#) [EG-2001CA 125.0000M-PCZS](#) [EG-2001CA 133.3333M-PCHLX](#) [EG-2001CA 158.0000M-PCZLX](#) [EG-2021CA 125.0000M-CGRNLX](#) [EG-2001CA 106.2500M-PCYB](#) [EG-2001CA 106.2500M-PCYL0](#) [EG-2001CA 167.0000M-PCHB](#) [EG-2001CA 133.3330M-PCHB](#) [EG-2001CA 120.0000M-PCHB](#) [EG-2021CA125.0000M-CGPNL0](#) [EG-2001CA120.0000M-PCHL0](#) [EG-2001CA120.0000M-PCHL3](#) [EG-2001CA133.0000M-PCHL0](#) [EG-2001CA133.3330M-PCHL0](#) [EG-2001CA167.0000M-PCHL0](#) [EG-2001CA167.0000M-PCHL3](#) [EG-2021CA 125.0000M-CGPNL0](#) [EG-2001CA 167.0000M-PCHL3](#) [EG-2001CA 120.0000M-PCHL0](#) [EG-2001CA 120.0000M-PCHL3](#)