

Memory Module Specifications

KSM32RD8/32MFR

32GB 2Rx8 4G x 72-Bit PC4-3200

CL22 Registered w/Parity 288-Pin DIMM

DESCRIPTION

Kingston's KSM32RD8/32MFR is a 4G x 72-bit (32GB) DDR4-3200 CL22 SDRAM (Synchronous DRAM) registered w/ parity, 2Rx8, ECC, memory module, based on eighteen 2G x 8-bit FBGA components. The SPD is programmed to JEDEC standard latency DDR4-3200 timing of 22-22-22 at 1.2V. Each 288-pin DIMM uses gold contact fingers. The electrical and mechanical specifications are as follows:

FEATURES

- Power Supply: VDD = 1.2V
- VDDQ = 1.2V
- VPP = 2.5V
- VDDSPD = 2.41V to 2.75V
- Functionality and operations comply with the DDR4 SDRAM datasheet
- 16 internal banks
- Bank Grouping is applied, and CAS to CAS latency (tCCD_L, tCCD_S) for the banks in the same or different bank group accesses are available
- Data transfer rates: PC4-3200, PC4-2933, PC4-2666, PC4-2400, PC4-2133, PC4-1866, PC4-1600
- Bi-Directional Differential Data Strobe
- 8 bit pre-fetch
- Burst Length (BL) switch on-the-fly BL8 or BC4(Burst Chop)
- Supports ECC error correction and detection
- On-Die Termination (ODT)
- Temperature sensor with integrated SPD
- This product is in compliance with the RoHS directive.
- Per DRAM Addressability is supported
- Internal Vref DQ level generation is available
- Write CRC is supported at all speed grades
- CA parity (Command/Address Parity) mode is supported

SPECIFICATIONS

CL(IDD)	22 cycles
Row Cycle Time (tRCmin)	45.75ns(min.)
Refresh to Active/Refresh Command Time (tRFCmin)	350ns(min.)
Row Active Time (tRASmin)	32ns(min.)
Maximum Operating Power	*
UL Rating	94 V - 0
Operating Temperature	0° C to +85° C
Storage Temperature	-55° C to +100° C

* See IDD Table (page2)

Module Assembly

DRAM: MICRON (F-DIE)




RCD: Rambus

Continued >>

IDD Specifications

Symbol	3200	Units
I _{DD0}	882	mA
I _{PP0}	45	mA
I _{DD1}	981	mA
I _{DD2N}	810	mA
I _{DD2NT}	801	mA
I _{DD2P}	684	mA
I _{DD2Q}	756	mA
I _{DD3N}	1098	mA
I _{PP3N}	36	mA
I _{DD3P}	900	mA
I _{DD4R}	1602	mA
I _{DD4W}	1350	mA
I _{DD5R}	954	mA
I _{PP5R}	54	mA
I _{DD6N}	954	mA
I _{DD6E}	1620	mA
I _{DD6R}	360	mA
I _{DD6A}	198	mA
I _{DD6A}	360	mA
I _{DD6A}	918	mA
I _{DD6A}	1620	mA
I _{PP6X}	108	mA
I _{DD7}	1845	mA
I _{PP7}	90	mA
I _{DD8}	648	mA

MODULE DIMENSIONS



The product images shown are for illustration purposes only and may not be an exact representation of the product.
Kingston reserves the right to change any information at anytime without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kingston:

[KSM32RD8/32MFR](#)