

Customer Specification

PART NO. 1219/50C

Construction

				Diameters (In)	
1) Component 1		50 X 1 COND			
a) Conductor		24 (7/32) AWG TC		0.024	
b) Insulation		0.010" Wall, Nom. PVC		0.044	
(1) Color Code		Alpha Wire Color Code D			
Cond	Color	Cond	Color	Cond	Color
1	BLACK	18	WHITE/GREEN	35	WHITE/RED/RED
2	RED	19	WHITE/YELLOW	36	WHITE/RED/GREEN
3	WHITE	20	WHITE/BLUE	37	WHITE/RED/BLUE
4	GREEN	21	WHITE/BROWN	38	WHITE/RED/BROWN
5	ORANGE	22	WHITE/ORANGE	39	WHITE/RED/VIOLET
6	BLUE	23	WHITE/SLATE	40	WHITE/GREEN/BLACK
7	BROWN	24	WHITE/VIOLET	41	WHITE/GREEN/RED
8	YELLOW	25	WHITE/BLACK/RED	42	WHITE/GREEN/GREEN
9	VIOLET	26	WHITE/BLACK/G	43	WHITE/GREEN/B

			REEN		LUE
10	SLATE	27	WHITE/BLACK/Y ELLOW	44	WHITE/GREEN/B ROWN
11	PINK	28	WHITE/BLACK/B LUE	45	WHITE/GREEN/V IOLET
12	TAN	29	WHITE/BLACK/B ROWN	46	WHITE/BLUE/BL ACK
13	RED/GREEN	30	WHITE/BLACK/O RANGE	47	WHITE/BLUE/RE D
14	RED/YELLOW	31	WHITE/BLACK/S LATE	48	WHITE/BLUE/GR EEN
15	RED/BLACK	32	WHITE/BLACK/VI OLET	49	WHITE/BLUE/BL UE
16	WHITE/BLACK	33	WHITE/BLACK/B LACK	50	WHITE/BLUE/BR OWN
17	WHITE/RED	34	WHITE/RED/BLA CK		
2) Cable Assembly		50 Components Cabled			
a) Twists:		2.3 Twists/foot (min)			
3) Shield:		Alum/Mylar Tape, 25% Overlap, Min.			
a) Foil Direction		Foil Facing Out			
b) Drain Wire		24 (7/32) AWG TC			
4) Jacket		0.032" Wall, Nom.,PVC		0.427 (0.452 Max.)	
a) Color(s)		SLATE			
b) Print		ALPHA WIRE-* P/N 1219/50C 50C 24 AWG SHIELDED 75C (UL) TYPE CM OR AWM 2576 --- LLXXXXXX CSA TYPE CMG FT4 CE ROHS * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]			

Applicable Specifications

1) UL	AWM/STYLE 2576	80°C / 150 V _{RMS}
	CM	75°C
	VW-1	
2) CSA International	CMG	60°C
	FT4	
3) CE:	EU Low Voltage Directive 2006/95/EC	

Environmental

1) CE: EU Directive 2011/65/EU(RoHS2):	
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011. No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C.
2) REACH Regulation (EC 1907/2006):	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.
3) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-20 to 80°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	179 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	300 V _{RMS}
2) Capacitance	45 pf/ft @1 kHz, Nominal Conductor to Conductor
3) Ground Capacitance	81 pf/ft @1 kHz, Nominal
4) Inductance	0.19 µH/ft, Nominal
5) Conductor DCR	26 Ω/1000ft @20°C, Nominal
6) OA Shield DCR	13.4 Ω/1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	24 x 14 x 12 Continuous length
b) 500 FT	18 x 12 x 8 Continuous length
c) 100 FT	12 x 10 x 5 Continuous length
	<i>[Spool dimensions may vary slightly]</i>

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARYNotice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document.

©2019 ALPHA WIRE - all rights reserved.



EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 1219/50C

1219/50C, RoHS-Compliant Commencing With 8/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014.

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) , Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

A handwritten signature in black ink, appearing to read 'Dave Watson'.

Dave Watson, Director of Engineering & QA

8/25/2020

Alpha Wire

711 Lidgerwood Ave.

Elizabeth, NJ 07207

Tel: 1-908-925-8000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Alpha Wire:

[1219/50C SL005](#) [1219/50C SL001](#)