

Customer Specification

PART NO. SPM1403CY

Construction

				Diameters (In)	
1) Component 1		3 X 1 COND			
a) Conductor		14 (41/30) AWG Bare Copper		0.074	
b) Insulation		0.016" Wall, Nom. PVC/ 0.005" Wall NYLON		0.116	
(1) Color Code		Alpha Wire Color Code F			
Cond	Color	Cond	Color	Cond	Color
1	BLACK	2	WHITE	3	RED
2) Cable Assembly		3 Components Cabled			
a) Twists:		3.4 Twists/foot (min)			
b) Orientation:		Components to be arranged from INSIDE LAYER to OUTSIDE LAYER			
c) Core Wrap		Clear Mylar Tape, 25% Overlap, Min.			
3) Shield		Tinned Copper BRAID Shield,85% Coverage, Min.			
4) Jacket		0.050" Wall, Nom.,PVC		0.381+/- 0.018	
a) Color(s)		GREEN			
b) Jacket Separator		Tissue Tape, 25% Overlap, Min.			
c) Print		ALPHA WIRE-* P/N SPM1403CY 3C 14 AWG (2.08mm2) SERIES SPM (UL) WTTC 90C DRY/WET 1000V OR (UL) TC-ER THWN-2 CDRS 90C DRY/WET 600V DIR BUR SUN RES OR MTW 14 AWG FLEXING --- C(RU) AWM I/II A/B 105C 600V FT1 CE ROHS (DATE CODE) (SEQ FOOTAGE) * = Factory Code			

Applicable Specifications

1) UL		
a) Component 1	THWN-2	90°C Dry / 90°C Wet / 600 V _{RMS}
b) Overall	UL 1277 TC	90°C Dry / 90°C Wet / 600 V _{RMS}
	UL 2277 WTTC	90°C Dry / 90°C Wet / 1000 V _{RMS}
	SUN RES	
	UL 1685 Vertical Tray Flame Test	
	UL 1063 MTW	90°C Dry / 60°C Wet / 600 V _{RMS}
	DIRECT BURIAL	
	EXPOSED RUN	
	OIL RES I	
2) CSA International	C(RU) AWM I/II A/B FT1	105°C / 600 V _{RMS}
3) Other		
a) Component 1	ASTM-B174 Class K	
4) CE:	EU Low Voltage Directive 2014/35/EU	

Environmental

1) CE: EU Directive 2011/65/EU(RoHS2), EU Directive 2015/863/EU (RoHS3):	
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011 and the amending Directive 2015/863/EU of 4 June 2015 . No Exemptions are required for RoHS Compliance on this item.
2) REACH Regulation (EC 1907/2006):	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-40 to 90°C(static), -30 to 90°C (dynamic)
2) Bend Radius	10X Cable Diameter
3) Pull Tension	103 Lbs, Maximum
4) Sunlight Resistance	Yes

5) Direct Burial	Yes
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	600/1000 V _{RMS}
2) Capacitance	49 pF/ft @1 kHz, Nominal Conductor to Conductor
3) Ground Capacitance	88 pF/ft @1 kHz, Nominal
4) Inductance	0.17 µH/ft, Nominal
5) Conductor DCR	2.6 Ω/1000ft @20°C, Nominal
6) OA Shield DCR	3.6 Ω/1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) Bulk(Made-to-order)	

www.alphawire.com

Alpha Wire | 1320 City Center Drive, Suite 100, Carmel, IN 46032

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document.

©2019 ALPHA WIRE - all rights reserved.



EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: SPM1403CY

SPM1403CY, RoHS-Compliant Commencing With 8/24/2009 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with UK - RoHS. The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014. This product is also in compliance with China RoHS 2 per GB/T 26572-2011.

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) ,	
Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

A handwritten signature in black ink, appearing to read 'Dave Watson'.

Dave Watson, Director of Engineering

12/14/2023

Alpha Wire

2200 US Highway 27 South

Richmond, IN 47374

Tel: 1-908-925-8000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[SPM1403CY GR001](#)