

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207 Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Request a Sample

Customer Specification PART NO. 5010/50C

Construction

		Diameters (In)
1) Component 1	50 X 1 COND	
a) Conductor	22 (7/30) AWG Tinned Copper	0.030
b) Insulation	0.010" Wall, Nom. PVC, Semi Rigid	0.050
(1) Color Code	Alpha Wire Color Code E	

Cond	Color	Cond	Color	Cond	Color
1	BLACK	18	WHITE/VIOLET	35	WHITE/RED/ORANGE
2	BROWN	19	WHITE/SLATE	36	WHITE/RED/YELLOW
3	RED	20	WHITE/BLACK/BROW N	37	WHITE/RED/GREEN
4	ORANGE	21	WHITE/BLACK/RED	38	WHITE/RED/BLUE
5	YELLOW	22	WHITE/BLACK/ORAN GE	39	WHITE/RED/VIOLET
6	GREEN	23	WHITE/BLACK/YELL OW	40	WHITE/RED/SLATE
7	BLUE	24	WHITE/BLACK/GREE N	41	WHITE/ORANGE/YEL LOW
8	VIOLET	25	WHITE/BLACK/BLUE	42	WHITE/ORANGE/GR EEN
9	SLATE	26	WHITE/BLACK/VIOLE T	43	WHITE/ORANGE/BLU E
10	WHITE	27	WHITE/BLACK/SLATE	44	WHITE/ORANGE/VIO LET
11	WHITE/BLACK	28	WHITE/BROWN/RED	45	WHITE/ORANGE/SLA TE
12	WHITE/BROWN	29	WHITE/BROWN/ORA NGE	46	WHITE/YELLOW/GRE EN
13	WHITE/RED	30	WHITE/BROWN/YELL OW	47	WHITE/YELLOW/BLU E
14	WHITE/ORANGE	31	WHITE/BROWN/GRE EN	48	WHITE/YELLOW/VIOL ET
15	WHITE/YELLOW	32	WHITE/BROWN/BLUE	49	WHITE/YELLOW/SLA TE
16	WHITE/GREEN	33	WHITE/BROWN/VIOL ET	50	WHITE/GREEN/BLUE
17	WHITE/BLUE	34	WHITE/BROWN/SLAT E		
2) Cable Assembly		50 Components Cable	d		
a) Twists:		2.5 Twists/foot (min)			
b) Orientation:	Components to be arranged from INSIDE LAYER to OUTSIDE LAYER				
c) Core Wrap		Nonwoven Polyester T	ape, 25% Overlap, Min.		

3) Jacket	0.032" Wall, Nom.,PVC	0.478 (0.503 Max.)
a) Color(s)	Slate, Black, Yellow, Orange, Blue, Green, Red, Sand Beige, White	
b) Ripcord	1 End 810 Denier Nylon	
c) Print	ALPHA WIRE-* P/N 5010/50C 50C 22 AWG XTRAGUARD(R) 1 (UL) TYPE CM 105C OR AWM 2464 80C 300V OR AWM 21894 105C 300V SUN RES 60C OIL VW-1 LLXXXXXX CSA 105C TYPE CMG FT4 CE ROHS (SEQ FOOTAGE) * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]	

Applicable Specifications

1) UL		
a) Component 1	AWM/STYLE 10002	105°C / 300 V _{RMS}
b) Overall	AWM/STYLE 21894	105°C / 300 V _{RMS}
	SUN RES	
	60C OIL	
	AWM/STYLE 2464	80°C / 300 V _{RMS}
	СМ	105°C
	VW-1	
2) CSA International	СМG	105°C
	FT4	
3) IEC	EN 60332-1 Flame Behavior	
	EN 60332-2 Flame Behavior	
4) CE:	EU Low Voltage Directive 2014/35/EC	

Environmental

1) CE: EU Directive 2011/65/EU(RoHS2), EU Directive 2015/863/EU (RoHS3):		
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011 and the amending Directive 2015/863/EU of 4 June 2015 . No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C.	
2) REACH Regulation (EC 1907/2006):		
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.	
3) California Proposition 65:	Exempt from warning labels based on the Consent Judgment. Please see Alpha's CA Prop 65 Statement for more information.	

Properties

Physical & Mechanical Properties		
1) Temperature Range	-35 to 105°C	
2) Bend Radius	10X Cable Diameter	
3) Pull Tension	275 Lbs, Maximum	
4) Sunlight Resistance	Yes	
Electrical Properties	(For Engineering purposes only)	
1) Voltage Rating	300 V _{RMS}	
2) Capacitance	23.5 pF/ft @1 kHz, Nominal Conductor to Conductor	
3) Inductance	0.18 µH/ft, Nominal	
4) Conductor DCR	16.7 Ω/1000ft @20°C, Nominal	

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	24 x 14 x 12 Continuous length
b) 500 FT	18 x 12 x 8 Continuous length
c) 100 FT	16 x 11 x 8 Continuous length
d) Bulk(Made-to-order)	
	[Spool dimensions may vary slightly]

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207 Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY

Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. ©2013 ALPHA WIRE - all rights reserved.



EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 5010/50C

5010/50C, RoHS-Compliant Commencing With 8/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3) The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item**. Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014.

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE),	
Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering & QA Alpha Wire 711 Lidgerwood Ave. Elizabeth, NJ 07207 Tel: 1-908-925-8000 3/25/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Alpha Wire:

5010/50C SL005 5010/50C SL001 5010/50C SL002