

## Customer Specification

### PART NO. 3050

## Construction

|                | Diameters (In)  |                |
|----------------|---|----------------|
| 1) Component 1 | 1 X 1 HOOKUP  |                |
| a) Conductor   | 24 (7/32) AWG Tinned Copper   | 0.024          |
| b) Insulation  | 0.016" Wall, Nom. PVC   | 0.056+/- 0.002 |
| (1) Print      | ALPHA WIRE E163869-* RU AWM STYLES 1569 105C<br>OR 1007 80C 300V VW-1 IEC 60332-2 24 AWG<br>OR CRU TR-64 90C FT1 CE ROHS<br>{0} * = Factory Code  |                |
| (2) Color(s)   | WHITE, BLACK, GREEN, YELLOW, BLUE, BROWN, ORANGE<br>SLATE, VIOLET, WHITE/BLACK, WHITE/RED<br>WHITE/GREEN, WHITE/YELLOW, WHITE/BLUE<br>WHITE/BROWN, WHITE/ORANGE, WHITE/SLATE<br>WHITE/VIOLET, GREEN/YELLOW, PINK, DK. BLUE<br>BROWN/BLACK, WHITE/PINK, BROWN/GREEN, BROWN/BLUE<br>RED |                |

## Applicable Specifications

|                      |                                     |                              |
|----------------------|-------------------------------------|------------------------------|
| 1) UL                | AWM/STYLE 1007                      | 80°C / 300 V <sub>RMS</sub>  |
|                      | AWM/STYLE 1569                      | 105°C / 300 V <sub>RMS</sub> |
|                      | VW-1                                |                              |
| 2) CSA International | TR-64                               | 90°C                         |
|                      | FT1                                 |                              |
| 3) IEC               | EN 60332-2 Flame Behavior           |                              |
| 4) CE:               | EU Low Voltage Directive 2014/35/EU |                              |

## Environmental

|  |  |
|--|--|
| 1) EU Directive 2011/65/EU(RoHS2), EU Directive 2015/863/EU (RoHS3): |  |
|  | All materials used in the manufacture of this part are in compliance with European Directive 2011/65/EU and the amending Directive 2015/863/EU of 4 June 2015 regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. |
| 2) REACH Regulation (EC 1907/2006):                                  |  |
|  | This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item.   |
| 3) California Proposition 65:  | This product may contain substances known to the State of California to cause Cancer or Reproductive Harm, but is exempt from labeling based on the Consent Judgement. See the Alpha Wire website for more information.  |
|  |  |

## Properties

| Physical & Mechanical Properties |                            |
|----------------------------------|----------------------------|
| 1) Temperature Range             | -40 to 105°C               |
| 2) Bend Radius                   | 10X Cable Diameter         |
| 3) Pull Tension                  | 3.5 Lbs, Maximum           |
| Electrical Properties            |                            |
| (For Engineering purposes only)  |                            |
| 1) Voltage Rating                | 300 V <sub>RMS</sub>       |
| 2) Inductance                    | 0.07 µH/ft, Nominal        |
| 3) Conductor DCR                 | 25 Ω/1000ft @20°C, Nominal |
|                                  |                            |

## Other

| Packaging  | Flange x Traverse x Barrel (inches)                             |
|--|---|
| a) 32800 FT  | 23 x 15 x 0 Max. 4 separate pieces; Min length/piece 10000 FT.  |
| b) 10000 FT  | 12 x 5.94 x 5 Max. 3 separate pieces; Min length/piece 1000 FT. |
| c) 5000 FT   | 10.5 x 5 x 3.5 Continuous length                                |
| d) 1000 FT   | 6.5 x 2 x 1.9 Continuous length                                 |
| e) 100 FT  | 2.75 x 2 x 1.125 Continuous length                              |
|  | <i>[Spool dimensions may vary slightly]</i>                     |
| Notes:   |   |
| a) Certain color and put-up combinations may only be available by special order. Minimums may apply. |   |
| b) Tolerance on 32800 ft. Put-Up is +/- 10%  |   |
|  |   |

[www.alphawire.com](http://www.alphawire.com)

Alpha Wire  
2200 US Highway 27 South  
Richmond, IN 47374

Tel: 1-800-52 ALPHA

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure the accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. <br /><br />  
©2019 ALPHA WIRE - all rights reserved.



## EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 3050

3050, RoHS-Compliant Commencing With 1/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above, including all packaging materials, is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with UK - RoHS. The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014. This product is also in compliance with China RoHS 2 per GB/T 26572-2011.

### Substance

|   |                           |
|---|---------------------------|
| Lead  | 0.1% by weight (1000 ppm) |
| Mercury   | 0.1% by weight (1000 ppm) |
| Cadmium   | 0.01% by weight (100 ppm) |
| Hexavalent Chromium   | 0.1% by weight (1000 ppm) |
| Polybrominated Biphenyls (PBB)                                | 0.1% by weight (1000 ppm) |
| Polybrominated Diphenyl Ethers (PBDE) ,<br>Including Deca-BDE | 0.1% by weight (1000 ppm) |
| Bis(2-ethylhexyl) phthalate (DEHP)                            | 0.1% by weight (1000 ppm) |
| Butyl benzyl phthalate (BBP)                                  | 0.1% by weight (1000 ppm) |
| Dibutyl phthalate (DBP)                                       | 0.1% by weight (1000 ppm) |
| Diisobutyl phthalate (DIBP)                                   | 0.1% by weight (1000 ppm) |

### Maximum Control Value

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering 11/30/2024

Alpha Wire  
2200 US Highway 27 South  
Richmond, IN 47374  
Tel: 1-908-925-8000

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[3050 BR005](#) [3050 RD005](#) [3050 BK005](#) [3050 WO001](#) [3050 BL005](#) [3050 WV001](#) [3050 WV005](#) [3050 WB005](#) [3050](#)  
[BL001](#) [3050 WS005](#) [3050 WS001](#) [3050 YL005](#) [3050 WY005](#) [3050 WO005](#) [3050 BK001](#) [3050 OR005](#) [3050 WY001](#)  
[3050 WH001](#) [3050 OR001](#) [3050 GR005](#) [3050 WH005](#) [3050 GR001](#) [3050 VI001](#) [3050 SL005](#) [3050 WR005](#) [3050](#)  
[SL001](#) [3050 GY005](#) [3050 WG005](#) [3050 RD001](#) [3050 BR001](#) [3050 VI005](#) [3050 YG001](#) [3050 BR013](#) [3050 SL013](#)  
[3050 RD013](#) [3050 BK013](#) [3050 BL013](#) [3050 PK005](#) [3050 WH013](#) [3050 VI013](#) [3050 OR013](#) [3050 GR013](#)