

Customer Specification

PART NO. 1550

Construction

	Diameters (In)	
1) Component 1	1 X 1 HOOKUP	
a) Conductor	24 (7/32) AWG Tinned Copper	0.024
b) Insulation	0.016" Wall, Nom. PVC	0.056+/- 0.002
(1) Color(s)	WHITE, BLACK, RED, GREEN, YELLOW, BLUE, BROWN ORANGE, SLATE, VIOLET, WHITE/BLACK, WHITE/RED WHITE/GREEN, WHITE/YELLOW, WHITE/BLUE WHITE/BROWN, WHITE/ORANGE, WHITE/SLATE WHITE/VIOLET	

Applicable Specifications

1) Military	MIL-W-76B TYPE MW	80°C / 1000 V _{RMS}
-------------	-------------------	------------------------------

Environmental

1) EU Directive 2011/65/EU(RoHS2), EU Directive 2015/863/EU (RoHS3):	
	All materials used in the manufacture of this part are in compliance with European Directive 2011/65/EU and the amending Directive 2015/863/EU of 4 June 2015 regarding the restriction of use of certain hazardous substances in electrical and electronic equipment.
2) REACH Regulation (EC 1907/2006):	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item.
3) California Proposition 65:	This product may contain substances known to the State of California to cause Cancer or Reproductive Harm, but is exempt from labeling based on the Consent Judgement. See the Alpha Wire website for more information.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-40 to 80°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	3.5 Lbs, Maximum
Electrical Properties	
(For Engineering purposes only)	
1) Voltage Rating	1000 V _{RMS}
2) Inductance	0.07 µH/ft, Nominal
3) Conductor DCR	25 Ω/1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	6.5 x 2 x 1.9 Continuous length
b) 100 FT	2.75 x 2 x 1.125 Continuous length
	<i>[Spool dimensions may vary slightly]</i>
Notes:	
a) Certain colors and put-up combinations may only be available by special order, minimums may apply.	

www.alphawire.com

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374

Tel: 1-800-52 ALPHA

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure the accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document.

©2019 ALPHA WIRE - all rights reserved.



EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 1550

1550, RoHS-Compliant Commencing With 1/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above, including all packaging materials is fully compliant with Directive 2011/65/EU, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This product also complies with Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with U definitions and extents of this Directive. **No Exemptions are required for RoHS Compliance on this item.** It should be noted that this product this Certificate is offered for cases where this product will be used within EEE that does fit within the Directive's scope. Additionally, Alpha c RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2006. This product is also in compliance w

Substance

Lead
Mercury
Cadmium
Hexavalent Chromium
Polybrominated Biphenyls (PBB)
Polybrominated Diphenyl Ethers (PBDE) ,
Including Deca-BDE
Bis(2-ethylhexyl) phthalate (DEHP)
Butyl benzyl phthalate (BBP)
Dibutyl phthalate (DBP)
Diisobutyl phthalate (DIBP)

Maximum Control Value

0.1% by weight (1000 ppm)
0.1% by weight (1000 ppm)
0.01% by weight (100 ppm)
0.1% by weight (1000 ppm)
0.1% by weight (1000 ppm)

0.1% by weight (1000 ppm)
0.1% by weight (1000 ppm)
0.1% by weight (1000 ppm)
0.1% by weight (1000 ppm)
0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the d general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legisl product.

Authorized Signatory for the Alpha Wire:

A handwritten signature in blue ink, appearing to be 'QBW' followed by a long horizontal stroke.

Dave Watson, Director of Engineering 11/30/2024

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374
Tel: 1-908-925-8000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[1550 WG005](#) [1550 WR005](#) [1550 RD005](#) [1550 GR001](#) [1550 BR001](#) [1550 SL001](#) [1550 BK005](#) [1550 VI005](#) [1550](#)
[BL001](#) [1550 RD001](#) [1550 OR005](#) [1550 OR001](#) [1550 VI001](#) [1550 BK001](#) [1550 GR005](#) [1550 BL005](#) [1550 BR005](#)
[1550 WG001](#) [1550 WO001](#) [1550 WR001](#) [1550 WV001](#) [1550 WY001](#) [1550 WS001](#) [1550 WY005](#) [1550 WS005](#)
[1550 WV005](#) [1550 WB005](#)