

Customer Specification

PART NO. 74010

Construction

						Diameter ("in")	
1) Component 1						1 x 4 PAIR	
a) Conductor						23 (SOLID) AWG Bare Copper	0.022
b) Insulation						0.009" Wall, Nom. Polyolefin	0.038
(1) Color(s)							
Pair	Color	Pair	Color	Pair	Color		
1	BLUE - WHITE/BLUE	3	GREEN - WHITE/GREEN				
2	ORANGE - WHITE/ORANGE	4	BROWN - WHITE/BROWN				
c) Pair						Bonded Pair	
(1) Twists						Staggered Lays	
d) Cabling						4 PAIR Cabled	
(1) Orientation						Parallel	
e) Jacket						0.018" Wall, Nom., PVC	
(1) Color(s)						WHITE	
(2) Ripcord						1 End 810 Denier Nylon	
2) Jacket						0.035" Wall, Nom., PVC	0.475X0.265
						(0.489X0.289 max.)	
a) Color(s)						BLACK	
b) Ripcord						1 End 810 Denier Nylon	
c) Print						ALPHA WIRE-* P/N 74010 4PR 23 AWG 75C (UL) CMR OR C(UL) CMR --- TIA-568-C.2 & ISO/IEC 11801 CAT 6 SUN RES OIL RES II --- US PATENT 6273977, 5821467 CE ROHS (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FT <i>Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.</i> * = Factory Code	

Applicable Specifications

1) UL	CMR	75°C
2) CSA International	C(UL) TYPE CMR	75°C
	FT4	
3) Other	TIA-568-C.2 Cat6 ISO/IEC 11801 Category 6	
4) CE	EU Low Voltage Directive 2014/35/EC	

Environmental

1) CE: EU Directive 2011/65/EU(RoHS2)	
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011and the amending Directive 2015/863/EU of 4 June 2015. No exemptions are required for RoHS Compliance on this item. Refer to the RoHS Certificate of Compliance for more detail.
2) REACH Regulation (EC 1907/2006)	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration .
3) California Proposition 65	Exempt from warning labels based on the Consent Judgment. Please see Alpha's CA Prop 65 Statement for more information.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-25 to 75°C
2) Bend Radius	4X Cable Diameter
3) Pull Tension	32 lbs. max.
4) Sunlight Resistance	Yes
5) Cable Weight	30 lbs./1000ft.
Electrical Properties	
	<i>Engineering purposes only</i>
1) Voltage Rating	300 V _{RMS}
2) Characteristic Impedance	100 ω +/- 15
3) Mutual Capacitance	15 pF/ft @1 kHz, Nominal
4) Velocity of Propagation	70%
5) Conductor DCR	27.4 ω/1000ft. @20°C, Nominal

Frequency(MHz)	Max. Attenuation(dB/100m)	Min. NEXT(dB)	Min. PSNEXT(dB)	Min. ACR(dB)
1	1.9	74.3	72.3	70
4	3.7	65.3	63.3	59
8	5.3	60.3	58.3	53
10	5.9	59.3	57.3	51
16	7.5	56.3	54.3	46
20	8.4	54.8	52.8	44
25	9.5	53.4	51.4	42
31.25	10.6	51.9	49.9	39
62.5	15.4	47.4	45.4	30
100	19.8	44.3	42.3	25
155	25.1	41.5	39.5	14
200	29	39.9	37.9	10

Frequency (MHz)	Min. PSACR(dB)	Min. RL(dB)	Min. ELFEXT(dB)	Min. PSELFEXT(dB)
1	70	20	67.8	64.8
4	59	23	55.7	52.7
8	53	24.5	49.7	46.7
10	51	25	47.8	44.8
16	46	25	43.7	40.7
20	44	25	41.7	38.7
25	42	24.3	39.8	36.8
31.25	39	23.6	37.9	34.9
62.5	30	21.5	31.8	28.8
100	25	21	27.8	24.8
155	14	21	23.9	20.9
200	10	21	21.7	18.7

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 500 FT	16 x 11 x 8 Continuous Length
	<i>Spool dimensions may vary slightly.</i>

www.alphawire.com

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374

Tel: 1-800-52 ALPHA

Although Alpha Wire (“Alpha”) makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document.

©2019 ALPHA WIRE - all rights reserved.



EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 74010

74010, RoHS-Compliant Commencing With 9/30/2013 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above, including all packaging materials, is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with UK - RoHS. The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014. This product is also in compliance with China RoHS 2 per GB/T 26572-2011.

Substance

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) , Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering 12/18/2024

Alpha Wire
2200 US Highway 27 South
Richmond, IN 47374
Tel: 1-908-925-8000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[74010 BK002](#)