





P.C. MOUNTING

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3	OPEN	2-1



CIRCUIT: SPDT

- NOTE:
- 1. ALL DIMENSIONS IN MM [INCH]
 - 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 - 3. TERMINAL NUMBERS FOR REF ONLY
 - ▲ 4. PLATING MATERIAL: SILVER
 - 5. RATING: 5A @ 120VAC OR 28VDC
2A @250VAC
 - 6. ELECTRIC LIFE: 40,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
 - 7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
 - 8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
 - 9. OPERATING TEMP.: -30°C to 85°C
 - 10. ▲ DENOTES CRITICAL PARAMETER.



ISOMETRIC

E-SWITCH®

D	14697	REVISED AND REDRAWN	2/17/05	AR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 100SP3T7B13M2QE				
SCALE 2:1	DATE 2/28/02	DR CJB	DWG T110318	REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[100SP3T7B13M2QE](#)