







SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	ON
2-3, 5-6	OPEN	2-1, 5-4



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- ▲ PLATING MATERIAL: GOLD
- RATING: 0.4VA @ 20VAC OR VDC MAX.
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
- DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL.
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT
- ▲ 12. SEAL RATED: IP 67
- ▲ 13. HARDWARE TO BE SHIPPED BULK
T200001 - HEXNUT (QTY 2)
T200000 - LOCKWASHER (QTY 1)
T200002 - LOCKRING (QTY 1)



C	18347	ADD FLANGE, CHAMFER TO BUSHING	12/11/08	BLR
B	18181	ACTUATOR / BUSHING HEIGHTS FINALIZED	7/18/08	BLR
A	18169	RELEASED FOR PRODUCTION	7/10/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE 200AWMDP1T1A4M2REH SPECIAL

SCALE 2:1

DATE 12/11/2008

DR BLR

DWG ST201117

REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[200AWMDP1T1A4M2REH](#)