

## Customer Specification

### PART NO. 9316

## Construction

						Diameter ("in")	
1) Component 1						1 x 1 COAX	
a) Conductor						25 (7/.0067) AWG SCW	0.020
b) Insulation						0.020" Wall, Nom. PTFE	0.060
(1) Color(s)							
Cond	Color	Cond	Color	Cond	Color		
1	CLEAR						
2) Shield						SPC BRAID Shield, 94% Coverage, min.	
3) Jacket						0.010" Wall, Nom., FEP	0.098 (0.102 max.)
a) Color(s)						NATURAL TAN	
b) Print						ALPHA WIRE-* P/N 9316 MIL-DTL-17 M17/113-RG 316 12814 E346462 1C 26 AWG SHIELDED 200C (UL) C(UL) CMG FT4 OR AWM 1971 150C 125V CE ROHS * = Factory Code <i>Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.</i>	

## Applicable Specifications

1) UL	AWM/STYLE 1971	150°C / 125 V <sub>RMS</sub>
	CMG	200°C
2) CSA International	C(UL) TYPE CMG	200°C
	FT4	
3) Military	MIL-C-17/113 RG 316/U	200°C / 900 V <sub>RMS</sub>
4) CE	EU Low Voltage Directive 2006/95/EC	

## Environmental

1) CE: EU Directive 2011/65/EU(RoHS2)	
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011. No exemptions are required for RoHS Compliance on this item. Refer to the <a href="#">RoHS Certificate of Compliance</a> for more detail.
2) REACH Regulation (EC 1907/2006)	
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see <a href="#">Alpha's REACH SVHC Declaration</a> .
3) California Proposition 65	Outer surface materials used in manufacturing this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-55 to 200°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	2.11 lbs. max.
Electrical Properties	
Engineering purposes only	
1) Voltage Rating	900 V <sub>RMS</sub>
2) Characteristic Impedance	50 ω +/- 2
3) Ground Capacitance	29.3 pf/ft @1 kHz, Nominal
4) Velocity of Propagation	70 %
5) Conductor DCR	85.8 ω/1000ft @20°C, Nominal
6) OA Shield DCR	8.5 ω/1000ft @20°C, Nominal
7) Voltage Withstanding	2 kV, min.
8) Corona Extinction	1.2 kV, min.
9) SRL	30 db @ 50 MHz
	30 @ 100 MHz
	23 @ 400 MHz
	21 @ 1 GHz
	17 db @ 3 GHz
10) Attenuation (max. dB/100ft)	7.5 @ 50 MHz
	11 @ 100 MHz
	21 @ 400 MHz
	38 @ 1 GHz
	58 @ 3 GHz

Other

--

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	9 x 4.5 x 3.5 max. 3 separate pieces; Min length/piece 100 FT.
b) 500 FT	6.5 x 4 x 2.5 max. 2 separate pieces; Min length/piece 100 FT.
c) 100 FT	3.5 x 3 x 1.125 Continuous Length
d) Bulk ( <i>made-to-order</i> )	Max. 3 pieces per 1000 FT./Min length 100 FT.
	<i>[Spool dimensions may vary slightly]</i>

[www.alphawire.com](http://www.alphawire.com)

Alpha Wire  
2200 US Highway 27 South  
Richmond, IN 47374

Tel: 1-800-52 ALPHA

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. <br /><br />  
©2019 ALPHA WIRE - all rights reserved.



## EU/UK/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 9316

9316, RoHS-Compliant Commencing With 8/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above, including all packaging materials, is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3). This product also complies with UK - RoHS. The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014. This product is also in compliance with China RoHS 2 per GB/T 26572-2011.

### Substance

Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) , Including Deca-BDE	0.1% by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)

### Maximum Control Value

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering 12/14/2024

Alpha Wire  
2200 US Highway 27 South  
Richmond, IN 47374  
Tel: 1-908-925-8000

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[9316 BR005](#)