



P.C.B. MOUNTING HOLES



CIRCUIT: SPD

CONTACT CONFIGURATION



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.00=±0.25
3. TERM. NOS. FOR REF ONLY
4. RATING: 3A @120VAC OR 28VDC; 1A @250VAC
5. ELECTRIC LIFE: 30,000 MAKE AND BREAK CYCLES AT FULL LOAD
6. INSULATION RESISTANCE: 1,000 MEGA-OHMS MIN
7. DIELECTRIC STRENGTH: 1,000V RMS @SEA LEVEL
8. OPERATING TEMP.: -30°C TO +85°C

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
$\langle DN \rangle$	OFF	$\langle DN \rangle$
$2-3$	$OPEN$	$2-1$

 $\langle \rangle = \text{MOMENTARY}$

7. FREEZING STORAGE: +1000V RMS 500A LEVEL				
8. OPERATING TEMP.: -30°C TO +85°C				
C	11498	REVISED ACTUATOR	5/11/01	CJB
B	11113	REVISED & REDRAWN	12/13/00	PML
REV.	ECN NO.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				
<div>E-SWITCH®</div>				
TITLE				
200 MSP-4 T1 B1 M2 Q E				
SCALE		DATE	DR	DWG
2:1		10/20/00	PML	T211083
				REV
				C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[200MSP4T1B1M2QE](#)