







PCB LAYOUT




▲ SWITCH FUNCTION

POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3	NONE	2-1

NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACTS: COPPER ALLOY W/ GOLD PLATING
- RATING: 0.4 VA max. @ 48V AC OR DC max.
- CONTACT RESISTANCE: <50 MILLI-OHM
- MECHANICAL LIFE: 40,000 CYCLES.
- INSULATION RESISTANCE: 1000 MEGA-OHM min.
- DIELECTRIC STRENGTH: 500 V RMS @SEA LEVEL.
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- SEAL RATING: IP67
- 2002/95/EC (ROHS) COMPLIANT



TITLE 200RSP3T1B1M7R

A	22045	New Release	11/6/15	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:1	DATE 10/20/2015	DR rc	DWG T240008	REV A
--------------	--------------------	----------	----------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[200RSP3T1B1M7R](#)