






P.C. MOUNTING

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	(ON)
2-3	OPEN	2-1



CIRCUIT: SPDT

- NOTE:
- 1. ALL DIMENSIONS IN MM [INCH]
 - 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 - 3. TERMINAL NUMBERS FOR REF ONLY
 - ▲ 4. PLATING MATERIAL: GOLD
 - 5. RATING: 0.4 VOLTAMPS MAX. @20V MAX. AC OR DC
 - 6. ELECTRIC LIFE: 50,000 make-and-break cycles at full load.
 - 7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
 - 8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
 - 9. OPERATING TEMP.: -30°C to 85°C
 - 10. ▲ DENOTES CRITICAL PARAMETER.



ISOMETRIC

E-SWITCH®

A	14391	RELEASED FOR PRODUCTION	10/6/04	AR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE 300SP2J4BLKM2RE				
SCALE 2:1	DATE 10/6/04	DR AR	DWG T312019	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[300SP2J4BLKM2RE](#)