SHEET 1 OF 1




PANEL CUTOUT
MAX. PANEL THICKNESS:
11.0 [.43 in]



▲

| SWITCH FUNCTION | |
|---|---|
| POS. 1 | POS. 2 |
| | |
| ON | ON |
| 1-3 | 1-2 |




SPDT ON-ON
CONTACT CONFIGURATION







NOTE:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
   X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
▲4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 55°C
▲11. TRAVEL: 2.8mm
12. ▲ DENOTES CRITICAL PARAMETER.
▲13. LAMP VOLTAGE: 1.8V (FORWARD), 2.8V (REVERSE)
14. INGRESS PROTECTION: IP65
15. HARDWARE SUPPLIED: O-RING AND HEXNUT

| REV | PCR NO | DESCRIPTION | DATE | BY |
|---|---|---|---|---|
| A | 23977 | RELEASE | 7/26/19 | MW |

*THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED*

E•SWITCH®

TITLE PV4F23011-3K1-M01

| SCALE | DATE | DR | DWG | REV |
|---|---|---|---|---|
| 3:2 | 7/26/2019 | MW | 52-PV4F230113K1M01 | A |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

PV4F23011-3K1-M01