



CIRCUIT: SPDT

SWITCH FUNCTION	
ON	<ON>
1-3	1-2

() = MOMENTARY

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NDS. FOR REF. ONLY
4. RATING: 1A @ 120VAC or 28VDC
5. CONTACT RESISTANCE: 10mILl-ohms initial
@2-4VDC
6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sea level
9. OPERATING TEMP.: -30°C to 85°C



				TITLE			
				700 SP-7 B11 M1 Q E/C1 BLK			
A	12448	RELEASED FOR PRODUCTION	9/25/02	CJB			
REV.	ECN NO.	DESCRIPTION	DATE	CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							
			SCALE	DATE	DR	DWG	REV
			2:1	9/25/02	CJB	XT0105P	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[700SP7B11M1QEC1BLK](#)