




## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. RATING: 12VDC @ 50mA
4. CONTACT RESISTANCE: 100m $\Omega$  MAX.
5. INSULATION RESISTANCE: 100M $\Omega$  MIN.
6. OPERATING FORCE: 160  $\pm$  50gf
7. TRAVEL: 0.2  $\pm$  0.1mm
8. OPERATING TEMPERATURE: -40°C to 85°C
9. OPERATING LIFE 500,000 CYCLES
- ▲ 10. LED COLOR: YELLOW
11. ▲ DENOTED CRITICAL PARAMETER
12. 2011/65/EU (ROHS) COMPLIANT
13. PACKAGE: SWITCHES ARE 450 PIECES PER REEL  
BUTTONS WILL BE BAGGED SEPARATE  
450 BUTTONS PER BAG.
14. PART TO BE HALOGEN FREE.
15. BUTTONS TO BE ASSEMBLED ONTO THE SWITCH AFTER SOLDERING.



ALL TERMINALS TO BE  
COPLANER WITHIN  
0.1mm(0.004")

LED SPECS	UNITS	YELLOW
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @ 20mA	V	2.0 TYP, 2.5 MAX
LUMINOUS INTENSITY @ 20mA	MCD	1800 TYP



E-SWITCH®

A	23541	New Release	9/5/18	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL3265YQSCLR

SCALE 4:1	DATE 9/4/2018	DR MW	DWG B200081	REV A
--------------	------------------	----------	----------------	----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL3265YQSCLR](#)