


Technical drawing of a mechanical part with the following dimensions and tolerances:


- Overall width: 5.08 [.200]
- Overall height: 8.13 [.320]
- Inner diameter: ϕ 6.10 [.240]
- Inner height: 4.39 [.173]
- Feature: FLAT





SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
<DN>	OFF	<DN>
2-3	OPEN	2-1

0.76 x 0.51 Thk.
[.030 x .020] Typ.

1. ALL DIMENSIONS IN MM [INCH] [0.030 x .020] TYP
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NO'S. FOR REF. ONLY
4. CONTACT RATING: 3A @120 VAC OR 28VDC, 1A @250VAC
5. ELECTRIC LIFE: 30,000 make-and-break cycles
at full load.
6. INSULATION RESISTANCE: 1,000 M ohm min.
7. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
8. OPERATING TEMP.: -30°C to 85°C
9. ▲ DENOTES CRITICAL PARAMETER.
10. 2002/95/EC (ROHS) COMPLIANT



				 	
TITLE				200MSP4T2B1M1QE	
B	19387	TERMINALS DRAWN AS M1, UPDATES	10/27/10	BLR	
A	13118	RELEASED FOR PRODUCTION	5/8/03	AR	
REV.	PCR No.	DESCRIPTION	DATE	CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
SCALE		DATE	DR	DWG	REV
2:1		5/8/03	AR	T221002	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[200MSP4T2B1M1QE](#)