



RECOMMENDED P.C.B. LAYOUT




CIRCUIT: SPDT  
CONTACT CONFIGURATION

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
<DN>	OFF	<DN>
2-3	OPEN	2-1

( ) = MOMENTARY

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 3A @120VAC OR 28VDC, 1A @250VAC
5. ELECTRIC LIFE: 30,000 make-and-break cycles  
at full load.
6. INSULATION RESISTANCE: 1,000 M ohm min.
7. CONTACT MATERIAL: SILVER
8. OPERATING TEMP. -30°C to 85°C
9. ▲ DESIGNATE MAJOR DIMENSION
10. 2002/95/EC (ROHS) COMPLIANT
11. HARDWARE TO BE SUPPLIED BULK:  
T200000-LOCK WASHER QTY-1  
T200002-LOCK RING QTY-1  
T200001-HEX NUT QTY-2



TITLE			
200MSP4T2BIM2QEH			
REV.	ECN No.	DESCRIPTION	DATE
A	17011	RELEASED FOR PRODUCTION	2/20/07
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE	DATE	DR	DWG
2:1	2/20/07	TN	ST211071
			REV
			A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[200MSP4T2B1M2QEH](#)