




CIRCUIT: SPDT




SWITCH FUNCTION			
PDS. 1	PDS. 2	PDS. 3	
			
DN	NONE	DN	
2-3	OPEN	2-1	

NOTES:


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.4V @20V AC or DC max.
5. FIXED TERMINAL/MOVING CONTACT:

Copper Alloy w/GOLD Plate over Nickel plate.

6. ELECTRICAL LIFE: 40,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sea level
9. OPERATING TEMP.: -30°C to +85°C
10. 2002/95/EC (ROHS) COMPLIANT
11. HARDWARE TO BE SUPPLIED IN BULK:
T100011-LOCK WASHER QTY-1
T100015-LOCK RING QTY-1
T100000-HEX NUT QTY-2



RECOMMENDED P.C.B. LAYOUT



T1000015-LOCK RING		QTY-1	
T1000000-HEX NUT		QTY-2	
B	17218	6.35 DIM CHANGED TO 6.6	4/24/07
A	15497	RELEASE	11/3/05
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TITLE		100SP11B1M2REH	
SCALE	DATE	DR	DWG
2:1	4/24/07	TN	ST111067
REV		B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

100SP1T1B1M2REH