










## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. RATING: 20VDC @ 1mA
4. CONTACT RESISTANCE: 200Ω MAX.
5. INSULATION RESISTANCE: 100MΩ MIN. @ 100VDC.
6. OPERATING FORCE: 125±35gf
7. TRAVEL: 1.3 +/- 0.3 mm
8. OPERATING TEMPERATURE: -20°C TO 70°C
9. OPERATING LIFE: 300,000 CYCLES
10. LED: GREEN
11. ▲ DENOTES CRITICAL PARAMETERS
12. 2002/95/EC (ROHS) COMPLIANT
13. CONTACT MATR'L: GOLD FLASH OVER NICKEL



| LED SPECS                 | UNITS | GREEN               |
|---------------------------|-------|---------------------|
| FORWARD CURRENT           | mA    | 20                  |
| FORWARD VOLTAGE @20mA     | V     | 1.7 MIN.   2.6 MAX. |
| LUMINOUS INTENSITY @ 20mA | mcd   | 120 TYP.            |

|     |        |                                       |          |     |
|-----|--------|---------------------------------------|----------|-----|
| C   | 20506  | Added Note For Gold Flash Over Nickel | 3/2/2012 | MM  |
| B   | 19590  | UPDATE PCB LAYOUT                     | 1/17/11  | BGL |
| A   | 18913  | Release For Production                | 3/3/10   | BLR |
| REV | PCR NO | DESCRIPTION                           | DATE     | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE LP15R1WHTGRN-N

SCALE 2 : 1

DATE 3/3/2010

DR BLR

DWG B270005

REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP15R1WHTGRN-N](#)