



▲ LED SPECS	UNITS	WHITE
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	3.5 - 4.0
LUMINOUS INTENSITY @ 10mA	MCD	2000





T	D
1.0-2.0	8.0-8.2
2.0-2.5	8.2-8.4
2.5-3.0	8.4-8.6



▲ WHITE LED
CIRCUIT: SPST
OFF (ON)

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- RATING: 30VDC @ 100mA
- CONTACT RESISTANCE: 50 mΩ MAX.
- INSULATION RESISTANCE: 100MΩ MIN @ 500VDC.
- OPERATING FORCE: 250 ± 100gf
- TRAVEL: 1.8±0.3mm
- OPERATING TEMPERATURE: -40°C TO 85°C
- OPERATING LIFE: 50,000 CYCLES
- LED: WHITE
- ▲ DENOTES CRITICAL PARAMETERS
- 2002/95/EC (ROHS) COMPLIANT



▲ WHITE MARK TO
INDICATE CATHODE
(-) LEAD ON LED



ISOMETRIC



A	20156	New Release	9/16/11	BGL
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP10A1AW

SCALE 2:1

DATE 9/16/2011

DR BGL

DWG B200204

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[LP1OA1AW](#)