


CIRCUIT: SPDT

## CONTACT CONFIGURATION


SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	ON
2-1	OPEN	2-3



## RECOMMEND P.C.B. LAYOUT

## NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
- TERM NOS. FOR REF. ONLY
- RATING: 5A @120VAC or 28VDC:  
2A @250VAC
- CONTACT MATERIAL:  
Copper ALloy w/Silver plate
- ELECTRICAL LIFE: 30,000 ACTUATIONS @Full Load
- INSULATION RESISTANCE: 1000 Mega Ohms min.
- DIELECTRIC STRENGTH: 1000V RMS @SEA LEVEL.
- OPERATING TEMPERATURE: -30°C TO 85°C

**E-SWITCH®**

TITLE

500SSP1S1M7QEA

SCALE

2:1

DATE

2/24/95

DR

AR

DWG

T511012

REV

C

THE INFORMATION CONTAINED IN THIS DOCUMENT  
IS PROPRIETARY TO E-SWITCH AND IS  
NOT TO BE COPIED OR TRANSFERRED

C	14535	REVISED AND REDRAWN	11/22/04	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[500SSP1S1M7QEA](#)