



CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING






NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: GOLD
5. CONTACT RATING: 0.3A @ 125VAC
6. CONTACT RESISTANCE: 50 Milli-OHMS MAX.
7. OPERATING FORCE: 800 ± 300 g/cm
8. OPERATING TEMP: -30°C TO 85°C
- ▲ 9. CIRCUIT SP: 11 POSITION - 30° INDEX (NON-SHORTING)
10. INSULATION RESISTANCE: 100 Mega-OHMS MIN.
11. DIELECTRIC STRENGTH: 500 VAC FOR 1 min..
- ▲ 12. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, STOP RING
13. ▲ DENOTES CRITICAL PARAMETER.
14. 2002/95/EC (ROHS) COMPLIANT.



ISOMETERIC



E-SWITCH®



TITLE KC51A9.501NPF

SCALE 1.5:1

DATE 9/29/2009

DR BLR

DWG G511017

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC51A9.501NPF](#)