







RECOMMENDED P.C.B. LAYOUT





CIRCUIT: 4PDT

SWITCH FUNCTION	
DN	<DN>
1-3~4-6	1-2~4-5

< > = MOMENTARY

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 1A @120V AC or 28VDC
5. FIXED TERM. & MOVING CONTACT:
Copper Alloy w/Silver plate
6. CONTACT RESISTANCE: 10mΩ—ohms initial
@2-4VDC
7. ELECTRICAL LIFE: 50,000 make—and—break
cycles at full load.
8. INSULATION RESISTANCE: 1,000M ohm min.
9. DIELECTRIC STRENGTH: 1000V RMS @sea level
10. OPERATING TEMP.: -30°C to 85°C



9. DIELECTRIC STRENGTH: 1000V RMS @sea level			
10. OPERATING TEMP.: -30°C to 85°C			
A	11614	RELEASED FOR PRODUCTION	8/14/01 CJB
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TITLE			
700 DP-7 B10 M2 Q E /C1 BLK CAP			
SCALE	DATE	DR	DWG
2:1	8/14/01	CJB	XT0087A
			REV
			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[700DP7B10M2QEC1BLK](#)