




▲ CIRCUIT: SPDT

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A @ 120VAC or 28VDC, 1A @ 250VAC
6. MECHANICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
7. CONTACT RESISTANCE: 50 mΩ MAX. INITIAL @ 2-4VDC
8. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN @ 1000VDC
9. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
10. OPERATING TEMP.: -40°C to 85°C
11. OPERATING FORCE: 350 $\pm$ 100gf
12. TRAVEL: Electrical Make: 1.34 $\pm$ 0.25mm / Full Travel: 1.88 $\pm$ 0.30mm
13. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
C	ECO-102680	print update	04/19/24	MW					000025961
					TITLE				800CSP1B6M6QE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV
					2:1	11/10/2015	rc	T835002	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[800CSP1B6M6QE](#)