






PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-.01 [7.56]
1.25-2.0 [0.049-.079]	19.4-.01 [7.64]
2.0-3.0 [0.079-.118]	19.8-.01 [7.80]



PANEL CUTOUT
NOT TO SCALE



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
<ON>	OFF	<ON>
1-1a	OPEN	1-1b



()=MOMENTARY

CIRCUIT: SPD

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR

6A @ 250VAC

APPROVALS: UL, CSA, NEMKO, SEMKO, FEMKO, DEMKO

5. MATERIALS: TERMINALS: Silver Plated Copper Alloy

CONTACTS: Coin Silver, Silver Plated


6. ELECTRIC LIFE: 10,000 cycles

7. CONTACT RESISTANCE: <20 Mega-ohm

8. INSULATION RESISTANCE: >1000 Mega-ohm

9. DIELECTRIC STRENGTH: >1500 V 1 minute

>3000 V between poles



E-SWITCH®

				TITLE	
				R19661 BLK BLK ES	
B	12061	REVISED AND REDRAWN	4/16/02	CJB	
REV.	ECN NO.	DESCRIPTION	DATE	CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
SCALE		DATE	DR	DWG	REV
1.5:1		4/16/02	CJB	M306203	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R1966IBLKBLKES](#)