






PARTS LIST

ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040009	D16OAR11
2	1	F050404	INCANDESCENT LAMP, 14VAC/DC
3	1	F050105	LENS, WHITE, ROUND CONCAVE



PANEL MOUNTING
PANEL THK. 0.5mm - 5.0mm



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A @ 250 VAC, 8A @ 125 VAC
6A @ 24 VDC
5. MECHANICAL LIFE: 2,000,000 OPERATIONS
6. INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
7. OPERATING TEMP.: -25°C to 55°C
8. LAMP TYPE: 14VAC/DC INCANDESCENT
9. ▲ DENOTES CRITICAL PARAMETER.
10. PACKAGE: BOX/20 PER



E-SWITCH®

A	23645	RELEASED FOR PRODUCTION	10/29/18	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE D16OAR11BWHT

SCALE 2:1	DATE 10/29/2018	DR MW	DWG XF0920P	REV A
--------------	--------------------	----------	----------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAR11BWHT](#)