









RECOMMENDED PANEL MOUNTING



## NOTE:

1. ALL DIMENSIONS IN MM [INCH].
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY.
- ▲ 4. CONTACT RATING: 5A @ 250VAC,  
8A @ 125VAC,  
6A @ 24VDC
5. ELECTRICAL LIFE: 50,000 OPERATIONS
6. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
- ▲ 7. CONTACT MATERIAL: SILVER PLATED COPPER ALLOY
8. ACTUATION FORCE: 300g / POLE
9. OPERATING TEMP.: -25°C to +55°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT

## PARTS LIST

| ITEM | QTY | PART NUMBER | DESCRIPTION                           |
|------|-----|-------------|---------------------------------------|
| 1    | 1   | F040008     | D16OAS11                              |
| 2    | 1   | F050314     | 50-003-14 RED LENS FLAT               |
| 3    | 1   | F050404     | 50-004-04 INCANDESCENT 14V AC/DC 80mA |



TITLE D16OAS11BRED

|     |        |                           |         |     |
|-----|--------|---------------------------|---------|-----|
| B   | 19790  | DRAWING CLEAN UP / UPDATE | 3/25/11 | BGL |
| REV | PCR NO | DESCRIPTION               | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |           |     |         |     |
|-------|-----------|-----|---------|-----|
| SCALE | DATE      | DR  | DWG     | REV |
| 1.5:1 | 3/25/2011 | BGL | XF0418P | B   |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAS11BRED](#)