

PVT4 SERIES ANTI-VANDAL SWITCH

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



APPLICATIONS / MARKETS




Consumer Electronics



Security Devices



Industrial Controls



Kiosks



Electrical Housewares



Medical Equipment

RoHS

SPECIFICATIONS

Electrical Rating: 50mA, 24VDC
Electrical Life: 500,000 Cycles
Contact Resistance: 50mΩ Max.
Insulation Resistance: 1000 MΩ Min.
Dielectric Strength: 250VAC
Operating/Storage Temperature: -25°C to 55°C
Travel: 0.5mm
Moisture Protection: IP65
Contact Arrangement: SPST Off-(On)
Actuation Force: 490 grams
Panel Thickness: 1-6mm
Mounting Nut Torque: 0.8Nm

FEATURES & BENEFITS

- 19mm panel cutout
- Solder or wire lead termination options
- Ring illumination
- LED color options
- Crisp tactile response
- IP65 rated

PART NUMBER CONFIGURATOR

Series	Actuator Options	Terminal Options	Function Options	Housing Options	Button Finish	Lens Style	LED Color	LED Voltage Options
PVT4	F - Flat	S - Solder Lug
W - Wire leads
300mm	4 - Off - (On)*	S - Stainless Stainless	S - Stainless Stainless	3 - Ring Illumination	0 - White
1 - Red
2 - Orange
3 - Green
4 - Blue
5 - Yellow	1 - Base Voltage
3 - 6V
4 - 12V
5 - 24V

NOTES:
 *(ON) Denotes function is momentary

Specifications subject to change without notice 6.5.2018



E-SWITCH®







www.e-switch.com

800.867.2717

1







PVT4 SERIES ANTI-VANDAL SWITCH

SOLDERLUG TERMINATION



PVT4 SERIES ANTI-VANDAL SWITCH

WIRE LEAD TERMINATION



E-SWITCH®

www.e-switch.com

800.867.2717

3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[PVT4FW4SS331](#) [PVT4FW4SS341](#) [PVT4FS4SS341](#) [PVT4FS4SS344](#) [PVT4FS4SS331](#) [PVT4FW4SS311](#)
[PVT4FS4SS334](#) [PVT4FS4SS311](#) [PVT4FS4SS314](#)