





SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
		
DN	NONE	<DN>
2-3,5-6 8-9	OPEN	2-1,5-4 8-7

$\langle \rangle$ = Momentary





CIRCUIT: 3PDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC OR 28VDC;
2A @250VAC
5. FIXED TERM. & MOVING CONTACT:

- ▲ 5. FIXED TERM, & MOVING CONTACT:
Copper Alloy w/Silver Plate.
- 6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
- 7. INSULATION RESISTANCE: 1,000M ohm min.
- 8. DIELECTRIC STRENGTH: 1000V RMS @sea level
- 9. OPERATING TEMP.: -30°C to 85°C
- ▲ 10. SUPPLIED HARDWARE - HEX NUT (2) LOCK RING,
AND LOCK WASHER.



E-SWITCH®

				TITLE			
				100 3P2 T6 B11 M1 Q E			
A	12273	RELEASED FOR PRODUCTION	6/27/02	CJB			
REV.	ECN No.	DESCRIPTION	DATE	CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED							
			SCALE	DATE	DR	DWG	REV
			2:1	6/12/02	CJB	T131026	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

1003P2T6B11M1QE