



CIRCUIT: 2P; SPST
CONTACT CONFIGURATION
ON-OFF (ILLUMINATED)





ACTUATOR: TRANSLUCENT
YELLOW LENS




RECOMMEND PANEL MOUNTING

SWITCH FUNCTION	
POS. 1	POS. 2
ON	OFF
2-1	OPEN



ALIGNMENT KEY



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A, 12 VDC MAX.
5. CONTACT RESISTANCE: 50m ohm max.
6. INSULATION RESISTANCE: DC 500V 100M ohm min.
7. DIELECTRIC STRENGTHS: AC 1500V 1 minute
8. OPERATING TEMP.: -20°C to 85°C
9. LED: 12V YELLOW
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT.

C	20589	CHANGED SCHEMATIC, AND DIM 22.80 WAS 22.60	05/04/12	DRG
B	17941	CHANGE TO TRANSLUCENT YELLOW LENS, 3 TERMS.	1/24/08	BLR
A	16814	RELEASED FOR PRODUCTION	1/8/2007	TN
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE

RR3112BBLKYELYELEF4 - SPECIAL

SCALE

2:1

DATE

1/8/2007

DR

BLR

DWG

F130512

REV

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[RR3112BBLKYELYELEF4](#)